

PRODUCT SPECIFICATION

Printed: 2/10/2014

Catalog : S1400

Sodium Phosphate, Dibasic, Anhydrous, Reagent, ACS

CAS# : 7558-79-4

Formula : Na₂HPO₄

Formula Weight : 141.96

Test

**Limit
Min. Max.**

	Limit Min. Max.
ASSAY (Na ₂ HPO ₄)	99.0 %
pH OF A 5% SOLUTION @ 25[dC	8.7 - 9.3
INSOLUBLE MATTER	-- 0.01 %
LOSS ON DRYING @ 105 C	-- 0.2 %
CHLORIDE (Cl)	-- 0.002 %
SULFATE	-- 0.005 %
HEAVY METALS (as Pb)	-- 0.001 %
IRON (Fe)	-- 0.002 %