

PRODUCT SPECIFICATION

Printed: 2/10/2014

Catalog : S1535

Stannous Chloride, Dihydrate, Crystal, Reagent, ACS

CAS# : 10025-69-1

Formula : SnCl₂[2H₂O

Formula Weight : 225.65

Test

Limit
Min. Max.

	98.0 - 103.0 %
ASSAY (SnCl ₂ .2H ₂ O)	98.0 - 103.0 %
SOLUBILITY IN HCl	-- TO PASS TEST
SULFATES (SO ₄)	-- TO PASS TEST
CALCIUM (Ca)	-- 0.005 %
POTASSIUM (K)	-- 0.005 %
SODIUM (Na)	-- 0.01 %
IRON (Fe)	-- 0.003 %
LEAD (Pb)	-- 0.01 %
EXPIRATION DATE	