

PRODUCT SPECIFICATION

Printed: 2/10/2014

Page 1 of 1

Catalog : S1962

Sodium Starch Glycolate, pH 5.5-7.5, Type A, NF

CAS# : 9063-38-1

| Test | Limit | |
|--------------------------|--------------|--------|
| | Min. | Max. |
| SODIUM (DRIED BASIS) | 2.8 - 4.2% | |
| pH (1g in 30ml of Water) | 5.5 - 7.5 | |
| MICROBIAL LIMITS | TO PASS TEST | |
| LOSS ON DRYING | -- | 10.0% |
| IRON (Fe) | -- | 0.002% |
| HEAVY METALS | -- | 0.002% |
| SODIUM CHLORIDE | TO PASS TEST | |
| SODIUM GLYCOLATE | -- | 2.0% |
| IDENTIFICATION | TO PASS TEST | |
| EXPIRATION DATE | | |
| RESIDUAL SOLVENTS | TO PASS TEST | |