

PRODUCT SPECIFICATION

Printed: 2/10/2014

Page 1 of 1

Catalog : Z1085

Zinc Oxide, USP

CAS# : 1314-13-2

Formula : ZnO

Formula Weight : 81.38

Test

Limit Min. Max.

ASSAY (ZnO)	99.0 - 100.5%
ALKALINITY	TO PASS TEST
LOSS ON IGNITION	-- 1.0%
CARBONATE AND COLOR OF SOLUTION	TO PASS TEST
ARSENIC (As)	-- 6 PPM
IRON AND OTHER HEAVY METALS	TO PASS TEST
LEAD (Pb)	TO PASS TEST
IDENTIFICATION	TO PASS TEST
RETEST DATE	
RESIDUAL SOLVENTS	TO PASS TEST