



Aerosol Metal, 11 oz.
078698133812

THRUST® STARTING FLUID

M3815

Use in Autos, Buses, Trucks, Tractors, Outboard Motors, Chain Saws & Construction Equipment. Easier starts for gasoline and diesel engines. Effective at -65°F. Contains upper cylinder lubricant. This diesel fuel additive complies with the federal low sulfur content requirements for use in diesel motor vehicles and non-road engines.

APPLICATIONS:

- Gas & Diesel Engines
- Quick Start In Extreme Cold Conditions Effective to -65°F

DIRECTIONS: DO NOT FLOOD ENGINE BEFORE USING. Follow engine manual recommendations. Improper use or use in some glow-plug diesels could cause engine damage or bodily harm. Step 1: Spray into air cleaner or carburetor for 3 seconds, and stand clear (Carburetor can backfire). Step 2: Start engine. Step 3: If unsuccessful, repeat steps 1 and 2 up to three times. Step 4: If engine fails to start, ignition should be checked by mechanic.

STORAGE, HANDLING & DISPOSAL: Do not expose to heat, sparks or open flames. Store in a dry, well-ventilated area below 120°F / 49°C. Do not puncture, crush or incinerate can. Do not keep container inside car or living area. Leaking cans should be disposed of immediately. Dispose of product, container and residue according to local, state and federal laws and regulations.

DANGER: EXTREMELY FLAMMABLE. FIRE AND EXPLOSION HAZARD: DO NOT USE NEAR HEAT, SPARKS, OR OPEN FLAME OR WITH OTHER CHEMICALS OR GASES SUCH AS OXYGEN. DO NOT SMOKE. Turn off sources of ignition (electrical motors, flames, pilot lights, heaters) before use and until vapors dissipate. Never use with ignition "ON." Container contact with battery terminals, solenoids, or electrical components can cause flash fire and serious injury. **BREATHING & INGESTION HAZARDS:** Use only in well-ventilated area. **INHALING CONCENTRATED VAPORS, INTENTIONALLY OR OTHERWISE MAY CAUSE DEATH WITHOUT WARNING.** Harmful or fatal if swallowed. **CONTACT HAZARD:** Avoid contact with eyes and skin. Prolonged skin contact may cause dermatitis.

FIRST AID: **EYE CONTACT:** Flush thoroughly with water for 15 minutes while lifting eyelids and get prompt medical attention. **SKIN CONTACT:** Wash with soap and water. If irritation persists, get prompt medical attention. **INHALATION:** Move to fresh air. If breathing becomes difficult, get prompt medical attention. **INGESTION:** DO NOT INDUCE VOMITING. Call Poison Control Center, Physician or Hospital Emergency Room immediately.

KEEP AWAY FROM CHILDREN AND ANIMALS

NOTICE: While this information is presented in good faith and believed to be accurate, Radiator Specialty Company does not guarantee satisfactory results from reliance thereon. The data is offered solely for your information and Radiator Specialty Company disclaims all liability for any loss or damage from its use. Thoroughly test any application according to the product directions and independently conclude satisfactory performance. Nothing contained herein is to be construed as a recommendation to use the product in violation of any patent.