

2005A, 2007A & 2008A

QUICK RESPONSE TURN-LOCK MOUNTING PHOTOCONTROL



SPECIFICATIONS

ON/OFF: Turn-ON is 1 to 3 fc. Turn-OFF to Turn-ON is 3 average.

TIME DELAY: Instant ON/3-5 seconds OFF.

CELL: Cadmium sulphide photocell responds to the light spectrum near to that of a human eye. Resists effects of moisture and airborne contaminants.

CONTACTS: Solid brass prongs for maximum corrosion resistance and electrical conductivity.

SURGE ARRESTOR: 360 joules MOV exceeds NEMA and ANSI requirements.

RELAY: Positive snap action switching, reducing bounce and prolonging contact life.

TEMPERATURE RANGE:
-40° to +158°F (-40° to +70°C).

FAIL MODE: ON.

WARRANTY: 3 years.

APPLICATIONS



- For use on streets, highways and other luminaries equipped with locking type receptacles, where instant response is required.

Complies with ANSI C136.10 and EEI NEMA standards.

FEATURES

STANDARDS: Meets ANSI C136.10 including color designations. Also meets EEI NEMA standards.

HOUSING: Polypropylene, UV Stabilized, permanent color with UV resistant clear acrylic window. Provides high impact, flammability resistance and electrically safe operation.

ENERGY SAVINGS: Works with screw base CFLs and LED lamps.

CONTACT RATINGS

CATALOG NO.	RATING	
	TUNGSTEN	BALLAST
2005A	1000W	1800VA
2007A	1000W	1800VA
2008A*	1000W	1800VA

ORDERING INFO

CATALOG NO.	UPC CODE	VOLTAGE 50-60Hz	COLOR
2005A	62012	105-130	Grey
2007A	62013	105-285	Blue
2008A*	62014	400-550	Yellow

*Not UL or CSA listed.

WIRING DIAGRAMS

