



PO Box 6180 • 6855 Hermosa Circle • Buena Park, CA 90622
Ph: 714-562-0500 • Fx: 714-562-0600 • TF: 1-888-TRIMLOK (874-6565)
Email: info@trimlok.com • Website: www.trimlok.com

Engineering Specifications for Rubber Seal

Description:	Rubber Seal comes in a variety of specially designed shapes, made from custom formulated EPDM sponge rubber compound.
Resistance Ratings:	Ozone – Excellent Water Absorption - Excellent Sunlight Aging - Excellent Low Temperature – Excellent Compression Set - Good
General Temperature Ratings:	-20° F to +150° F
Compression Rating:	Trim-Lok recommends 25% compression for maximum performance.
Density:	21 to 23 PCF
Flammability & Code Compliance:	FMVSS 302 UL94HB
UL Certification:	File # MH49032 - UL50
Adhesive Options:	<p>“BT” 3M High Strength Adhesive - This 3M Acrylic Automotive grade tape creates the ultimate bond to the rubber and substrate. Creates a moisture barrier and airtight seal between rubber and substrate. Highest peel and shear resistance can be used under high loads of stress and force. Has low initial tack for easy re-positioning during installation and needs 72 hours of cure time to come to full bond strength. Good heat performance -20° F to +150° F.</p> <p>“HT” Pressure Sensitive Adhesive - This Acrylic based adhesive is best used to hold the rubber seal in place while installing it in a static application or compressed between two stationary objects. May be used in some light duty dynamic applications against a variety of substrates. Good heat performance -20° F to +150° F. During application ambient temperature must be above +60° F.</p>

Trim-Lok®, Inc. warrants all products to be free from defects in material and workmanship for a period of ninety (90) days from date of purchase. This warranty does not include damage to products resulting from accident, misuse, improper installation or storage, and unauthorized alterations. Trim-Lok's warranty obligation shall be limited to furnishing substitute products for original products, which in Trim-Lok's sole judgement, have proven defective in material or workmanship within the ninety (90) day warranty period. Any implied warranties of merchantability or propriety for any particular purpose, shall be strictly limited in duration to that of the express warranty set forth above. In no event shall Trim-Lok be liable for any special, incidental or consequential damages resulting from the manufacture, sale, or use of these products under any legal theory. Said damages shall include, but not be limited to, lost profits, damage to property, or damages for personal injury. Trim-Lok's liability shall in no case exceed the price paid for the product claimed to be defective. All information contained herein is the property of Trim-Lok Inc. Possession of this document does not convey any rights to transmit such information, or to use, to sell or manufacture from such information. No reproduction or publication of this document shall be made without written authorization from Trim-Lok Inc.