

Nes[®] Sets

Universal Thread Repair Tool

Nes1000 External External 4-38 mm $\frac{5}{32}$ " - $1\frac{1}{2}$ "

Model	Cat. #	Contents		Packaged Size			Weight		
				L	W	H	lb	gm	
Nes 1000	01000	Nes external 1A Nes External 2	RK 1 60° RK 2 60°	inch	10 $\frac{1}{16}$ "	6"	1 $\frac{13}{16}$ "	2.7	1200
				mm	256	152	46		



Nes1300 External External 4-152 mm $\frac{5}{32}$ " - 6"

Model	Cat. #	Contents		Packaged Size			Weight		
				L	W	H	lb	gm	
Nes 1300	01300	Nes external 1A Nes External 2 Nes External 3 Nes Cleaner Nes 3 extension handle	RK 1 60° RK 2 60° RK 3 60°	inch	17"	9 $\frac{1}{2}$ "	2 $\frac{9}{16}$ "	8.4	3750
				mm	430	240	65		



Nes1007 Internal Internal 8-20 mm $\frac{5}{16}$ " - $\frac{13}{16}$ "

Model	Cat. #	Contents		Packaged Size			Weight		
				L	W	H	lb	gm	
Nes 1007	01007	Nes Internal 21 Nes Internal 22 Nes Internal 23	RK 21 60° RK 22 60° RK 23 60°	inch	10 $\frac{13}{16}$ "	8 $\frac{1}{16}$ "	1 $\frac{15}{16}$ "	1.9	860
				mm	275	205	50		



Nes1008 Internal Internal 8-32 mm $\frac{5}{16}$ " - $1\frac{1}{4}$ "

Model	Cat. #	Contents		Packaged Size			Weight		
				L	W	H	lb	gm	
Nes 1008	01008	Nes Internal 21 Nes Internal 22 Nes Internal 23 Nes Internal 24	RK 21 60° RK 22 60° RK 23 60° RK 24 60°	inch	10 $\frac{13}{16}$ "	8 $\frac{1}{16}$ "	1 $\frac{15}{16}$ "	2.9	1300
				mm	275	205	50		



Nes1036 Internal Internal 22-68 mm $\frac{7}{8}$ " - $2\frac{5}{8}$ "

Model	Cat. #	Contents		Packaged Size			Weight		
				L	W	H	lb	gm	
Nes 1036	01036	Nes Internal 24 Nes Internal 25 Sleeve 07259 Sleeve 07269	RK 24 60° RK 25 60° F RK 26 60° F RK 26 60° C	inch	10 $\frac{13}{16}$ "	8 $\frac{1}{16}$ "	1 $\frac{15}{16}$ "	4.4	2000
				mm	275	205	50		

