

Total Lighting Solutions

Brilliantly Engineered To Work as Smart as You

WOBBLELIGHT

The **NEW** LED Wobblelight is up to 20% more energy efficient than the standard Wobblelight making this light ideal for projects where energy consumption is a concern. The LED Wobblelight is still bright and dependable with all the durability you expect from Wobblelight.

- 36 watt LED bulb
- Self-righting up to 45°
- Low heat output-no hot surfaces that can cause burns
- 360° lighting adjustable to 180° with optional reflector
- No set-up required
- Convenience receptacle for connecting units in a series



Specifications / Model	11136LED
Lamp Type	LED
Watts	36
Lumen Output	3,625
Max. Lighting Range	30 ft.
Amps @ 110V	.9
Lamp Life (Avg.)	25,000 hrs
Weight	29 lbs

Applications

- *High-rise & building construction*
- *Commercial / residential construction*
- *Renovation / demolition / remediation*
- *Industrial maintenance & turn-arounds*
- *Tank and vessel inspection / repair*
- *Aircraft & ship building / maintenance*
- *Emergency / disaster response*

