

Clutch style bar clamps



Simply better.

BESSEY® Clutch style bar clamps are a popular regular-duty clamp used by cabinet makers, woodworkers, metal workers and homecrafters across North America. These easy-to-use clamps are suitable for "close quarters" clamping.

Features & Benefits

- Powder coated, ductile cast iron jaws
- Nickel plated, serrated rail
- 2 piece slip clutch plates keep the jaw sturdy and in place.
- Non-marring pads on the top and bottom jaws
- Ergonomically shaped, standard wood handle, with our 2K comfort handle now available in the most popular GSCC3 models.



Single head, clutch style bar clamps (GSCC)

Wood handle is standard with our 2K comfort handle now available in the most popular models.

NEW

2K Handle	Wood Handle	Clamping Capacity	Throat Depth	Clamping Force	Approx. Weight
	GSCC2.506	6"	2 ½"	600 lbs	0.66 lbs
	GSCC2.512	12"	2 ½"	600 lbs	0.77 lbs
	GSCC2.518	18"	2 ½"	600 lbs	0.92 lbs
	GSCC2.524	24"	2 ½"	600 lbs	1.00 lbs
	GSCC2.530	30"	2 ½"	600 lbs	1.20 lbs
	GSCC2.536	36"	2 ½"	600 lbs	1.33 lbs
GSCC3.506+2K	GSCC3.506	6"	3 ½"	1100 lbs	1.12 lbs
GSCC3.512+2K	GSCC3.512	12"	3 ½"	1100 lbs	1.25 lbs
GSCC3.518+2K	GSCC3.518	18"	3 ½"	1100 lbs	1.38 lbs
GSCC3.524+2K	GSCC3.524	24"	3 ½"	1100 lbs	1.55 lbs
GSCC3.536+2K	GSCC3.536	36"	3 ½"	1100 lbs	1.72 lbs
	GSCC5.012	12"	5"	1200 lbs	2.08 lbs
	GSCC5.018	18"	5"	1200 lbs	2.25 lbs
	GSCC5.024	24"	5"	1200 lbs	2.50 lbs



Clutch style with double jaw (DHBC)

The double jaw clamp can do things other clamps can't. Very useful on corner glue ups and delicate work where pressure needs to be dispersed.

	Clamping Capacity	Throat Depth	Clamping Force	Approx. Weight
DHBC-12	12"	3 ½"	400 lbs.	2.20 lbs.
DHBC-24	24"	3 ½"	400 lbs.	2.80 lbs.
DHBC-36	36"	3 ½"	400 lbs.	3.40 lbs.

Rev. Jun/14

