SIEMENS

Data sheet US2:P1E42MC250CT

	Siemens Low Voltage RP1 Unassembled Lighting Panel. Dimensions (H x W x D) IN: 44.0 x 20.0 x 5.75. 3-Phase 4-Wire allows 42 circuits user selects Main Device (Lug/Breaker). Rated 480Y/277V (250A). Special features: tin-plated copper main bus, subfeed space included
suitability for operation	Lighting Loads/ Branch Circuit Loads
product brand name	SIEMENS
product type designation	UPB interiors
material of the enclosure	Copper BUS
certificate of suitability	PB1/UL67

last modified: 3/6/2020

Subject to change without notice
© Copyright Siemens