

# Product data sheet

## Characteristics

# QO115DFC

Mini circuit breaker, QO, 15A, 1 pole, 120VAC, 10kA, dual function, pigtail, plug in mount, clam pack



### Main

Product	Miniature circuit-breaker
Range	QO
Current Rating	15 A
Voltage Rating	120 V AC
Mounting Type	Plug-in
Number of Poles	1P
Circuit Breaker Type	Combination ARC-fault and ground fault
Ratings	HACR rated
Electrical Connection	Pressure plate
Connections Terminals	Pigtail neutral
Type of Packing	Clam packaging

### Complementary

Interrupt Rating	10 kA 120 V AC 50/60 Hz
Number of Panel Spaces	1
Wire Size	AWG 14...AWG 8 copper or aluminium
Tightening Torque	40.71 lbf.in (4.6 N.m)
Height	4.76 in (121 mm)
Width	0.75 in (19 mm)
Depth	2.91 in (74 mm)
Net Weight	0.56 lb(US) (0.254 kg)

### Environment

Certifications	UL Listed CSA
Ambient Rating	104 °F (40 °C)

### Ordering and shipping details

Category	01318-QO 1 POLE BULK BRKRS.
Discount Schedule	CPQ
GTIN	785901401667
Returnability	Yes
Country of origin	MX

### Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	1.00 in (2.54 cm)
Package 1 Width	4.10 in (10.414 cm)
Package 1 Length	7.00 in (17.78 cm)
Package 1 Weight	8.96 oz (254.0 g)
Unit Type of Package 2	CAR
Number of Units in Package 2	3
Package 2 Height	3.90 in (9.906 cm)
Package 2 Width	4.80 in (12.192 cm)

Package 2 Length	8.40 in (21.336 cm)
Package 2 Weight	31.04 oz (879.968 g)

### Offer Sustainability

California proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to <a href="http://www.P65Warnings.ca.gov">www.P65Warnings.ca.gov</a>
REACH Regulation	<a href="#">REACH Declaration</a>
EU RoHS Directive	Compliant <a href="#">EU RoHS Declaration</a>
Mercury free	Yes
China RoHS Regulation	<a href="#">China RoHS Declaration</a>
RoHS exemption information	<a href="#">Yes</a>