
Wimbledon | E34616-LC

Job Name:_____ Job Type:_____ Quantity:_____ Comments:_____



PRODUCT DESCRIPTION

Balancing work and play, the Wimbeldon collection is a fun collection of lighting fixtures that utilizes dual-layered sound dampening felt shades that enhance the acoustics of a space. The deep ridged pattern gracefully intersects elevating the simple forms. Choose from linear or half dome configurations in various colors: Dark Grey and Light Cream felts offer more neutral tones while the Olive exterior with Black felt interior presents a more colorful option. Housed within the shades are high powered LED modules that provide ample functional down lighting.



*max overall height

MEASUREMENTS

DIMENSION	: 39.75" L x 39.75" W x 5" H
MAX OAH	: 129.75" OAH
CANOPY	: 5" W x 2.5" H x 20.75" L
HANGING WEIGHT	: 4.2 lb

LAMPING

INPUT VOLTAGE	: 120V
LUMENS	: 1,550 Rated (1,000 Del.)
BULB	: 1 x 25W LED DC Integrated , 25W Total
BULB INCLUDED	: (Integrated)
DIMMABLE	:
CRI	: 90 CRI
COLOR_TEMP	: 3000K

FINISHES OPTION

- Dark Gray (DG)
- Light Cream (LC)
- Olive (OLV)

MATERIAL

PET Felt

RATINGS

cETLus
DRY Location

ADDITIONAL

RATED LIFE 25000 Hours
OPERATING TEMPERATURE:
-20°C (-4°F), 40°C (104°F)

PHOTOMETIC: Report Found Online

Always consult a qualified electrician before installing any lighting product.

ET2 Contemporary Lighting™

WESTERN DISTRIBUTION CENTER (HEADQUARTER)
253 NORTH VINELAND AVE I CITY OF INDUSTRY, CA 91746

EASTERN DISTRIBUTION CENTER
101 GARDNER PARK | PEACHTREE CITY, GA 30269

P. 626.956.4200 I F. 626.956.4225 I maximlighting.com