



EAN:	4013288120694	Size:	104x44x24 mm
Part number:	05003607001	Weight:	74 g
Article number:	8790 HMC	Country of origin:	TW
		Customs tariff number:	82042000

- 1/2" Zyklop socket
- For manual and power tool operations (non-impact)
- Knurling at lower end to enable easy gripping when used in manual applications
- Equipped with ball stop groove
- With Take it easy tool finder: colour coding by size

The Wera manual and machine socket (ISO 2725 part 3) can be used in manual and machine operations. With Take it easy tool finder with colour coding by size - for quick and easy identification of the required tool. Slip-proof for easy grip even with oily hands. With ball stop groove. For external hexagon screws and bolts. Made of matte chrome-plated chrome-vanadium.

Web link

<https://www.wera.de/en/05003607001>

Wera - 8790 HMC
05003607001 - 4013288120694

Wera Werkzeuge GmbH
Korzter Straße 21-25
D-42349 Wuppertal
Tel: +49 (0)2 02 / 40 45-0
E-Mail: info@wera.de

Take it easy tool finder system

Manual and machine sockets



Incredibly fast Zyklop Speed ratchet with pivoting ratchet head and 5 predefined locking positions









Take it easy tool finder system - with profile and size colour-coding for quick and easy tool selection. Colour-coded system for hexagon drive screws (L-Keys, Zyklop bit sockets), external hex drive screws and nuts (Joker wrenches, Zyklop sockets and Zyklop bit sockets with holding function), and TORX® drive screws (L-Keys, Zyklop bit sockets).



The manual and machine sockets can be used both for hand and power tools use (non-impact). Users need just one socket set for all applications.

Further versions in this product family:

							
		mm	inch	mm	mm	mm	mm
05003601001	leuchtgelb_yello wC	10.0	-	37.0	15.5	24.0	17.0
05003602001	cyan_2985C	11.0	-	37.0	16.5	24.0	17.0
05003603001	schwarz_blackC	12.0	-	37.0	17.5	24.0	17.0
05003604001	tuerkis_339C	13.0	-	37.0	19.0	24.0	17.0
05003605001	pink_241C	14.0	-	37.0	20.0	24.0	17.0
05003606001	weiss	15.0	-	37.0	21.0	24.0	17.0
05003607001	violett_2735C	16.0	-	37.0	22.5	24.0	17.0
05003608001	rot_200C	17.0	-	37.0	24.0	26.0	17.0
05003609001	leuchtgruen_37 5C	18.0	-	37.0	25.0	26.0	17.0
05003610001	blau_307C	19.0	-	37.0	26.5	26.0	20.0
05003611001	leuchtpink_232 C	20.0	-	37.0	28.0	26.0	20.0
05003612001	gruen_363C	21.0	-	37.0	29.0	26.0	20.0
05003613001	leuchtgelb_yello wC	22.0	-	37.0	30.5	26.0	20.0
05003614001	cyan_2985C	24.0	-	37.0	33.0	28.0	20.0

Web link

<https://www.wera.de/en/05003607001>

Wera - 8790 HMC

05003607001 - 4013288120694

Wera Werkzeuge GmbH

Korzter Straße 21-25

D-42349 Wuppertal

Tel: +49 (0)2 02 / 40 45-0

E-Mail: info@wera.de

05003615001	schwarz_blackC	27.0	-	40.0	36.5	32.0	23.0
05003616001	tuerkis_339C	30.0	-	42.0	40.0	34.0	25.0
05003617001	pink_241C	32.0	-	42.0	42.0	36.0	25.0
05003618001	rot_200C	-	3/8"	37.0	15.5	24.0	17.0
05003619001	violett_2735C	-	7/16"	37.0	16.5	24.0	17.0
05003620001	tuerkis_339C	-	1/2"	37.0	19.0	24.0	17.0
05003621001	pink_241C	-	9/16"	37.0	20.0	24.0	17.0
05003622001	weiss	-	19/32"	37.0	21.0	24.0	17.0
05003623001	schwarz_blackC	-	5/8"	37.0	22.5	24.0	17.0
05003624001	cyan_2985C	-	11/16"	37.0	25.5	26.0	17.0
05003625001	gelb_123C	-	3/4"	37.0	26.5	26.0	20.0
05003626001	leuchtpink_232 C	-	25/32"	37.0	28.0	26.0	20.0
05003627001	blau_307C	-	13/16"	37.0	29.0	26.0	20.0
05003628001	leuchtgruen_37 5C	-	7/8"	37.0	30.5	26.0	20.0
05003629001	rot_200C	-	15/16"	37.0	33.0	28.0	20.0
05003630001	violett_2735C	-	31/32"	37.0	33.0	28.0	20.0
05003631001	tuerkis_339C	-	1"	40.0	36.5	32.0	23.0
05003632001	pink_241C	-	1 1/16"	40.0	36.5	32.0	23.0
05003633001	weiss	-	1 1/8"	40.0	40.0	34.0	23.0
05003634001	schwarz_blackC	-	1 3/16"	42.0	40.0	34.0	25.0
05003635001	cyan_2985C	-	1 1/4"	42.0	42.0	36.0	25.0

Web link
<https://www.wera.de/en/05003607001>

Wera - 8790 HMC

05003607001 - 4013288120694

Wera Werkzeuge GmbH

Korzter Straße 21-25

D-42349 Wuppertal

Tel: +49 (0)2 02 / 40 45-0

E-Mail: info@wera.de