



**MCR
SAFETY**

BearKat (BK3) Safety Glasses

Value Series Specification Sheet

PRODUCT DESCRIPTION:

The BearKat® BK3 features a soft, secure gel nosepiece for additional comfort. It's super well thought-out construction combines the best in safety, comfort, and affordability! Your vision is unobstructed by the one-piece wraparound lens, which by its tight fit allows you maximum safety. Comfort is enhanced by the flexible temples and the non-slip temple sleeves, which are notched for a clip-on breakaway cord! The UV-AF® Anti-Fog coated lens are Eco-friendly and UV cured, providing 3 times greater Anti-Fog performance than generic Anti-Fog safety glasses. Choose the best safety glasses, choose MCR Safety!



To learn more about our anti-fog styles and anti-fog coating options [click here!](#)

FEATURES:

- Soft, secure gel nosepiece
- Single lens design with integral side shields for unobstructed view
- Non-Slip soft temple material
- UV-AF® anti-fog lens
- Exclusive Duramass® scratch resistant coating
- Rugged polycarbonate lens filters 99.9% of harmful U.V. rays

TECHNICAL DATA FOR: BK310AF

| | | | |
|--------------------------|--------------------------|--------------------|------------|
| Series | BearKat (BK3) | ANSI Z87+ | Yes |
| Category | Safety Glasses | | |
| Anti-Fog | Yes | | |
| Scratch Resistant | Yes | | |
| Packaging | White Inner Box | | |
| Case Pack | 144 | Case Weight | 14.076 lb. |
| Case Dimensions | 22.047 x 14.567 x 13.386 | Made In | Taiwan |

| | | | | | | | |
|-----------------|----------------------|----------------------|---------------------------|--------------|---------------------|----------------------|-----------------------|
| Item No: | Lens Options: | Lens Coating: | Scratch Resistant: | VLT%: | Frame Color: | Temple Color: | Temple Sleeve: |
|-----------------|----------------------|----------------------|---------------------------|--------------|---------------------|----------------------|-----------------------|

MCR Safety - 1255 Schilling Blvd. W. - Collierville, TN 38017 - USA

Phone: 901-795-5810 - Toll Free: 800-955-6887 - Fax: 800-999-3908 - Web: www.mcrcsafety.com

©2021 MCR Safety - All Rights Reserved



MCR
SAFETY

BearKat (BK3)

Safety Glasses

Value Series

Specification Sheet

| Item No: | Lens Options: | Lens Coating: | Scratch Resistant: | VLT%: | Frame Color: | Temple Color: | Temple Sleeve: |
|----------|------------------|--------------------|--------------------|-------|--------------|---------------|----------------|
| BK310 | Clear | Duramass Hard Coat | Yes | 90 | N/A | Clear | Black |
| BK310AF | Clear | UV-AF Anti-Fog | Yes | 90 | N/A | Clear | Black |
| BK312 | Gray | Duramass Hard Coat | Yes | 13 | N/A | Gray | Black |
| BK312AF | Gray | UV-AF Anti-Fog | Yes | 13 | N/A | Gray | Black |
| BK313 | Light Blue | Duramass Hard Coat | Yes | 68 | N/A | Light Blue | Black |
| BK314 | Amber | Duramass Hard Coat | Yes | 80 | N/A | Amber | Black |
| BK317 | Silver Mirror | Duramass Hard Coat | Yes | 13 | N/A | Smoke | Black |
| BK318 | Blue Mirror | Duramass Hard Coat | Yes | 13 | N/A | Smoke | Black |
| BK319 | I/O Clear Mirror | Duramass Hard Coat | Yes | 36 | N/A | Clear | Black |

MCR Safety - 1255 Schilling Blvd. W. - Collierville, TN 38017 - USA

Phone: 901-795-5810 - Toll Free: 800-955-6887 - Fax: 800-999-3908 - Web: www.mcrcsafety.com

©2021 MCR Safety - All Rights Reserved