



TEGERA® 811

Learn more

ESD PROTECTION AND PU DIPPED ON THE ENTIRE PALM

A soft, supple and airy glove for work where ESD protection is required. Palm dipped with PU gives really good precision and good grip. Knitted with 15 gg in thin and comfortable materials for comfortable use all day. Integrated size marking through the color of the cuff.

CHARACTERISTICS

- Extremely good fingertip sensitivity
- Extra flexible
- Extra comfortable

FUNCTIONS

- ESD
- Antistatic/ATEX
- Conforms with IEC 61340-5-1 (ESD)
- Thin

OEKO TEX® STANDARD 100 SE 14-214 RISE

All values for the specified product are indicated without tolerances and may vary to actual value for individual products. We reserve the right to modify or update the information in this document without prior notice.

PREVENTS RISK OF

Abrasion injuries, Scratches, lacerations, Antistatic

PRIMARY ENVIRONMENTS OF USE

Dry environments, Clean environments

PRIMARY AREAS OF USE

Electronics work, Fine assembly, Inspection work, Installation work

PRIMARY INDUSTRIES OF USE

Automotive manufacturing, Electrical equipment manufacturing, Electronics manufacturing, Machinery and equipment manufacturing, Metal manufacturing and fabrication, Transport equipment manufacturing

TYPE OF WORK

Light weight

SPECIFICATION

TYPE ESD gloves, Precision work gloves
CATEGORY Cat. II
KNITTING GAUGE (GG) 15
LINING MATERIAL Carbon, Nylon
LENGTH 220-250 mm
DEXTERITY 5
GRIP DESIGN Smooth finish
COLOUR Grey
PAIRS PER: BUNDLE/CARTON 12/120
DISPLAY TYPE Bulk pack
DIPPING Palm-dipped
DIPPING MATERIAL PU
CUFF STYLE Rolled edges
CUFF MATERIAL Textile
INNER MATERIAL SPECIFICATION Nylon, Carbon thread
OUTER MATERIAL SPECIFICATION Polyurethane

COMPLIANCE

CE Cat. II

EAC TP TC 019:2011

EN ISO 21420:2020

EN 388:2016+A1:2018 3131X

IEC 61340-5-1:2016 R < 1.0 x 10^9 Ω

EN 16350:2014 R < 1,0 x 10^8 Ω

ANSI 3 ABR

SIZE		ARTICLE NUMBER	EAN
6	XS	811-6	7392626007987
7	S	811-7	7392626007994
8	M	811-8	7392626008014
9	L	811-9	7392626008021
10	XL	811-10	7392626016569

ejendals
Limavägen 28, SE-793 32 Leksand, Sweden
Phone +46 (0) 247 360 00 | info@ejendals.com | order@ejendals.com

All values for the specified product are indicated without tolerances and may vary to actual value for individual products. We reserve the right to modify or update the information in this document without prior notice.