

# HIGHCLERE

MDS2404-AGB/OW

---

## FINISHES

---

**AGED BRASS w/ OFF-WHITE (MDS)**

Coastal Suitable Finish (EPM): No

## DIMENSIONS

---

Height: 12"

Width/Diameter: 12.75"

Minimum Height: 15.25"

Maximum Height: 67"

Canopy/Backplate: 5.25"

Hanging Type: 54" Chain

Product Weight: 9.9lb

Canopy/Backplate Shape: Round

Sloped Ceiling Compatible: Yes

Living Finish: No

Uplight Only: No

## Shade

---

Shade 1: Glass

Shade 1 Finish: Clear Optic

Shade 1 Top Width: 12"

Shade 1 Height: 1.5"

## ELECTRICAL

---



### Bulb 1

Bulb Included: No

Socket: E26 Medium Base

Bulb Type: A19

Max Wattage: 15

Bulb Quantity: 1

Bulb Included: No

Wire Length: 120"

Cord Type: SPT-1 SILVER W/ TINNED GROUND  
WIRE

Gem Box Required (2"x3"): No

Dark Sky: No

## SHIPPING

---

Carton 1: 16" x 16" x 15"

Carton 1 Weight: 13lb

Shipping Method: Ground

Country of Origin: VN

