

KEN

F3460-VGL

The mobile-inspired Ken family channels kinetic energy with natural materials and curved silhouettes. Each laminated coconut fiber shade wraps around a light source, highlighting the organic texture of the airy, sculptural forms. A Vintage Gold Leaf frame introduces a note of polish. Available as a 1-light sconce and a 6-light chandelier.

*Due to the one-of-a-kind nature of the medium, exact colors and patterns may vary slightly from the image shown.

FINISHES

VINTAGE GOLD LEAF

Coastal Suitable Finish (EPM): No

DIMENSIONS

Height: 11"

Width/Diameter: 60"

Minimum Height: 19.75"

Maximum Height: 55.5"

Canopy/Backplate: 6"

Hanging Type: 1-6" / 2-12" / 1-18" Stems

Product Weight: 14.3lb

Canopy/Backplate Shape: Round

Sloped Ceiling Compatible: No

Living Finish: No

Uplight Only: No

Shade

Shade 1: Natural Woven

Shade 1 Finish: Coconut Fiber

Shade 1 Top Width: 5"

Shade 1 Bottom L/W: 0" / 3"

Shade 1 Height: 12"

ELECTRICAL



Bulb 1

Bulb Included: No

Socket: E12 Candelabra Base

Bulb Type: G16.5

Max Wattage: 10

Bulb Quantity: 6

Wire Length: 144"

Cord Type: B & W TEFLON W/ GROUND WIRE

Gem Box Required (2"x3"):

Dark Sky: No

SHIPPING

Carton 1: 55" x 52" x 17"

Carton 1 Weight: 38lb

Shipping Method: Truck Only

Country of Origin: PH

