Vetra | E30481-BK

Job Name:_____ Job Type:_____ Quantity:_____ Comments:_____








PRODUCT DESCRIPTION

Vetra brings refined clarity to outdoor illumination with a simple cylindrical form and beautifully layered glass. A clear ribbed glass shade surrounds an omnidirectional LED light tube encased in Matte White acrylic, creating an even glow with subtle texture and depth. Finished in Matte Black, the streamlined frame adds crisp architectural contrast while allowing the illuminated column to remain the focus. Wet rated and offered in three sizes, Vetra delivers elegant, modern lighting for entries, patios, corridors, and exterior walls.



MEASUREMENTS

DIMENSION	: 4.75" W x 13.25" H x 4.5" Ext
BACK PLATE	: 4.75" W x 4.75" H x 7" HCO
HANGING WEIGHT	: 3.08 lb

LAMPING

INPUT VOLTAGE	: 120-277V
LUMENS	: 1,920 Rated (900 Del.)
BULB	: 3 x 8W LED DC Integrated , 24W Total
BULB INCLUDED	: (Integrated)
DIMMABLE	: Triac or ELV at 120V
CRI	: 90 CRI
COLOR_TEMP	: 3000K
LIGHTING_DIRECTION	: Vertical

FINISHES OPTION

Black (BK)

MATERIAL

Aluminum, Glass,,Acrylic

RATINGS

cETLus
Wet Location

ADDITIONAL

INSTALL UP/DOWN: Vertical
RATED LIFE 25000 Hours
OPERATING TEMPERATURE: -20°C (-4°F), 40°C (104°F)

Always consult a qualified electrician before installing any lighting product.

ET2 Contemporary Lighting™

WESTERN DISTRIBUTION CENTER (HEADQUARTER)
253 NORTH VINELAND AVE I CITY OF INDUSTRY, CA 91746

EASTERN DISTRIBUTION CENTER
101 GARDNER PARK | PEACHTREE CITY, GA 30269

P. 626.956.4200 I F. 626.956.4225 I maximlighting.com