



## YA312N, 350 kcmil, CU, 2 Hole, 1/2 Stud, 1.75 Spacing, Long

By Burndy  
Catalog # [YA312N](#)

350 kcmil, CU, 2 Hole, 1/2" Stud, 1.75" Spacing, Long Barrel, Tin Plated, Red / 18 or 324 Index



### Features

- Barrel designed with internal chamfer at wire entry for smooth insertion of wire, preventing possible damage of the strands
- Long barrel length allows for an increased number of crimps increasing the mechanical strength of the connection
- Electro-tin plated unless otherwise specified to reduce galvanic corrosion (bimetallic) and resist corrosive elements
- Connectors are clearly marked with stamping and barrel color coding
- 2-Hole design prevents rotation

### Application

Wire Termination

### Specifications

Certification - UL Recognized	No
Buy American Compliant	No
Certification - cULus	No
EU RoHS Indicator	Yes
Buy America(n) Qualified	TAA Compliant (All status valid till December 2026)
Industry Standard(s)	UL 486A-486B
Certification - ETL	No
Standards - Industry Standards Met	UL 486A-486B
Standards - RoHS Compliance Status	CM
UL Listed	Yes
Certification - CSA Approved	Yes

### Conductor

Conductor - Material	COPPER
Conductor - Copper Str Size	350 kcmil
Conductor Size	350 kcmil
Conductor Type	CODE
Conductor - Copper Str Size Range	350 kcmil

### Configuration

Physical Attribute - Number of Holes	2
Number of Pad Holes	2
Connector Type	LONG BARREL

### Current

Voltage Rating	35 kV
Voltage - Maximum	35000

### Dimensions

Dimension - Pad Width inch	1.29 in
Package Height	0.000 in
Dimension - Hole Size fraction	1/2
Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in
Dimension - L Length Overall mm	144 mm
Dimension - Outside Diameter inch	0.88 in
Dimension - Hole Size mm	14 mm
Dimension - Hole Size inch	0.56
Dimension - Strip Length inch	2-1/16
Dimension - Stud Size inch	1/2
Dimension - Stud Size fraction	1/2
Dimension - Bolt Hole Size inch	0.52 in
Dimension - Bolt Size fraction	1/2
Physical Attribute - Tongue Angle	Straight
Dimension - B Length fraction	2 in
Dimension - Z inch	0.63 in
Dimension - B Length inch	2.00 in
Dimension - N inch	0.62 in
Dimension - Bolt Size inch	0.5
Dimension - Length Overall inch	5.69 in

### General

Trade Name	HYLUG™
Die Index	18
Feature - Barrel Type	Long
Feature - Barrel Style	Chamfered
Plated	Y
Color Code	Red
Physical Attribute - Tongue Type	Standard
Sub Brand	HYLUG
UPC	781810505205
Type	Long Barrel, Tin Plated
Material	Copper

Plating Type Tin  
Finish Type Tin-Plated  
UPC 12 Digit 781810505205  
UPC 14 Digit GTIN 00781810505205

Carton Quantity 10

### Product Assets

[Catalog \[English\]](#)  
[Installation Manual \[English\]](#)  
[Installation Manual \[French, English\]](#)

### Logistics

Minimum Pack Quantity 1

---



A Hubbell brand