L-, HMCP (L) and (M) Frames and Shunt Trip

	Factory Mounted Connection Type and Location 18-Inch (457.2 mm) Pigtail Leads				Field Mounted Field Installation Kits ①	
	Same Side	Rear ②	Opposite Side	Terminal Block Same Side	Pigtail Leads	Terminal Block
Voltage Rating (AC Frequency = 50/60 Hz)	**Suffix Number**	**Suffix Number**	**Suffix Number**	**Suffix Number**	**Catalog Number**	**Catalog Number**
Left-Pole Mounting AC/DC Ratings ②						
12–24 Vac or Vdc	**S01**	**S02**	**S03**	**S04**	**SNT4LP03K**	**SNT4LT03K**
48–60 Vac	**S05**	**S06**	**S07**	**S08**	**SNT4LP05K**	**SNT4LT05K**
48–60 Vdc	**S85**	**S86**	**S87**	—	**SNT4LP23K**	**SNT4LT23K**
110–240 Vac	**S09**	**S10**	**S11**	**S12**	**SNT4LP11K**	**SNT4LT11K**
110–125 Vdc	**S41**	**S42**	**S43**	**S44**	**SNT4LP26K**	**SNT4LT26K**
380–440 Vac or 220–250 Vdc	**S13**	**S14**	**S15**	**S16**	**SNT4LP14K**	**SNT4LT14K**
480–600 Vac	**S17**	**S18**	**S19**	**S20**	**SNT4LP18K**	**SNT4LT18K**
Right-Pole Mounting AC/DC Ratings ③						
12–24 Vac or Vdc	**S21**	**S22**	**S23**	**S24**	**SNT4RP03K**	**SNT4RT03K**
48–60 Vac	**S25**	**S26**	**S27**	**S28**	**SNT4RP05K**	**SNT4RT05K**
48–60 Vdc	**S88**	**S89**	**S90**	—	**SNT4RP23K**	**SNT4RT23K**
110–240 Vac	**S29**	**S30**	**S31**	**S32**	**SNT4RP11K**	**SNT4RT11K**
110–125 Vdc	**S45**	**S46**	**S47**	**S48**	**SNT4RP26K**	**SNT4RT26K**
380–440 Vac or 220–250 Vdc	**S33**	**S34**	**S35**	**S36**	**SNT4RP14K**	**SNT4RT14K**
480–600 Vac	**S37**	**S38**	**S39**	**S40**	**SNT4RP18K**	**SNT4RT18K**

Notes

① Listed with Underwriters Laboratories, for field installation under E64983.
② Standard mounting location—leads exit rear of breaker.
③ For use with LT (thermal-magnetic) three-pole trip units only.