NEXFENCE

HYBRID POST SOLUTION™

BUILT DIFFERENT.
BUILT TO LAST.

Revolutionary hybrid base combines a wooden top with a heavy-duty, non-deteriorating base post constructed of steel rebar, high-density polyurethane foam, and a PVC covering that resists moisture, pests, decay, disease, and rotting.



NEXFENCE.COM

MADE IN USA

AFA American Fence Association

WHAT'S INSIDE MAKES THE DIFFERENCE



TOP
WOOD POST
Traditional strength above ground

SOIL FILL LINE

EXTERIOR
PVC JACKET
Moisture, pest & UV resistant plus landscaping protection

CORE
POLYURETHANE FOAM
Rot, fungal & decay-resistant core

REINFORCEMENT
STEEL REBAR
Heavy-duty load-bearing support below ground

ONE POST. ENDLESS APPLICATIONS.

- MAILBOXES
- ANIMAL FEEDERS
- FENCING
- BOUNDARY MARKERS
- LANDSCAPING
- SIGNAGE

VIEW GALLERY ONLINE!

Limited Lifetime Guarantee | Patent # 10,851,561

LEARN MORE AT NEXFENCE.COM