



jalas® E-SPORT 1615

ASTM F2413-18 M/I/C/SD 35/PR EN ISO 20345:2011 S3, SRC, CI

Learn more

A light, comfortable and attractive safety shoe with water-repellent properties and highest (S3) protection. The PU-coated and split leather upper and ventilating inner sole offer excellent safety and ergonomics. The oil-resistant PU outer sole gives outstanding grip in the slip, while our JALAS® aluminium toe cap, Plasma treated textile puncture protection and keep feet safe.

CHARACTERISTICS

- Excellent grip
- Perfect fit
- Extra comfortable
- Good shock absorption
- Light

FUNCTIONS

- Low weight
- Oil-resistant outsole
- Anti-static properties
- Polstered shaft edge
- Ventilating insole
- Water repellent
- Reflector
- Double shock absorption zones
- Conforms with IEC 61340-5-1 (ESD)

LEATHER WORKING GROUP

All values for the specified product are indicated without tolerances and may vary to actual value for individual products. We reserve the right to modify or update the information in this document without prior notice.

PREVENTS RISK OF

Toe injuries, Nail penetration, Antistatic

PRIMARY ENVIRONMENTS OF USE

Outdoors, Indoors, Environments with risk for outsole penetration

SPECIFICATION

TYPE Safety footwear, Low shoes
CATEGORY Cat. II
NAIL PROTECTION MATERIAL Plasma-treated composite (PTC) textile
FITTING Regular
COLLECTION E-Sport
UPPER MATERIAL PU-coated leather, Split leather
TOECAP MATERIAL Aluminium
LINING MATERIAL Polyester, polyamide
INSOLE JALAS FX2 Classic
INNERSOLE MATERIAL Textile, Soft EVA, Polyester-based conductive thread, Shock absorption zone in Ergothan
OUTSOLE MATERIAL PU outsole
FASTENING Laces
SHOELACES LENGTH 100 cm
COLOUR Black
NET WEIGHT, (SIZE 42) 1.11 kg

COMPLIANCE

CE Cat. II

ASTM F2413-18
M/I/C/SD 35/PR

EAC

EN ISO 20345:2011
S3, SRC, CI

TP TC 019:2011

FEATURES

- Aluminium toecap
- Nail protection in plasma-treated composite (PTC) textile
- Water repellent
- Oil-resistant outsole
- Ergothan Shock Absorption System
- Stabilizator
- Anti-static properties
- ESD

SIZE				ARTICLE NUMBER	EAN
EU	UK	US M	US W		
36	3	4	5	1615-36	6408487438394
37	4	5	6	1615-37	6408487438400
38	5	5.5	6.5	1615-38	6408487438417
39	6	6.5	7.5	1615-39	6408487438424
40	6.5	7.5	8.5	1615-40	6408487438431
41	7	8	9	1615-41	6408487438448
42	8	9	10	1615-42	6408487438455
43	9	9.5	11	1615-43	6408487438462
44	10	10.5	11.5	1615-44	6408487438479
45	10.5	11	12.5	1615-45	6408487438486
46	11	12	13	1615-46	6408487438493
47	12	13	14	1615-47	6408487438509

ejendals
Limavägen 28, SE-793 32 Leksand, Sweden
Phone +46 (0) 247 360 00 | info@ejendals.com | order@ejendals.com

All values for the specified product are indicated without tolerances and may vary to actual value for individual products. We reserve the right to modify or update the information in this document without prior notice.