Ziggurat | E51042-WT

Job Name:_____ Job Type:_____ Quantity:_____ Comments:_____









PRODUCT DESCRIPTION

Two tiers appear to spiral in this series of flush mounts. Finished in matte White, this subtle form is available in 3 sizes including an extra large 31.5" diameter bright enough for hospitality applications.





MEASUREMENTS

DIMENSION	: 19.75" L x 19.75" W x 4.75" H
HANGING WEIGHT	: 12 lb

LAMPING

INPUT VOLTAGE	: 120-277VV
LUMENS	: 4,410 Rated (2,000 Del.)
BULB	: 1 x 63W LED DC Integrated , 63W Total
BULB INCLUDED	: (Integrated)
DIMMABLE	: 3-in-1: Triac, ELV, or 0-10V
CRI	: 90 CRI
COLOR_TEMP	: 3000K

FINISHES OPTION

White (WT)

MATERIAL

Steel,PC

RATINGS

cETLus
Damp Location

ADDITIONAL

RATED LIFE 50000 Hours
OPERATING TEMPERATURE:
-20°C (-4°F), 40°C (104°F)

Always consult a qualified electrician before installing any lighting product.

ET2 Contemporary Lighting™

WESTERN DISTRIBUTION CENTER (HEADQUARTER)
253 NORTH VINELAND AVE I CITY OF INDUSTRY, CA 91746

EASTERN DISTRIBUTION CENTER
101 GARDNER PARK | PEACHTREE CITY, GA 30269

P. 626.956.4200 I F. 626.956.4225 I maximlighting.com