

EVERMORE

F1941-PBR

A nature-inspired take on timeless silhouettes, Evermore is defined by its airy, voluminous shape, graceful arcing arms, and petite off-white linen shades. Each fixture appears to reach upward—evoking the gentle growth of wild mushrooms. A Patina Brass finish adds warmth and vintage polish. Available as a 1-light sconce, 6- and 10-light chandeliers, and a 4-light linear, Evermore is a sculptural lighting fantasy for the modern home.

FINISHES

PATINA BRASS

Coastal Suitable Finish (EPM): No

DIMENSIONS

Height: 29.75"

Width/Diameter: 40.5"

Minimum Height: 30.25"

Maximum Height: 78.5"

Canopy/Backplate: 6"

Hanging Type: 1-6" / 2-12" / 1-18" Stems

Product Weight: 13lb

Canopy/Backplate Shape: Round

Sloped Ceiling Compatible: No

Living Finish: No

Uplight Only: No

Shade

Shade 1: Fabric

Shade 1 Finish: Off White Linen

Shade 1 Top Width: 2"

Shade 1 Bottom L/W: 0" / 9"

Shade 1 Height: 9"

ELECTRICAL



Bulb 1

Bulb Included: No

Socket: E12 Candelabra Base

Bulb Type: B11

Max Wattage: 10

Bulb Quantity: 6

Wire Length: 144"

Cord Type: B & W TEFLON W/ GROUND WIRE

Gem Box Required (2"x3"): No

Dark Sky: No

SHIPPING

Carton 1: 30" x 28" x 16"

Carton 1 Weight: 25lb

Shipping Method: Ground

Country of Origin: VN

