



Project / Job Name:

Location:

Fixture Type:

Notes:

**S14410** - 15 Watt LED A19; 27K/3K/35K/4K/5K CCT;  
Medium Base; Plastic; 12-24 Volt AC; 12-34 Volt DC;  
1-Pack



#### GENERAL

|                           |                                   |
|---------------------------|-----------------------------------|
| Company                   | SATCO                             |
| EA Height                 | 4.72                              |
| EA Width                  | 2.4                               |
| EA Length                 | 2.4                               |
| Material                  | Plastic                           |
| Fixture Type              | Miniature                         |
| Status                    | Active                            |
| Surge Protection          | Built-in-surge protection - 0.5KV |
| Total Harmonic Distortion | <150%                             |
| CCT Selectable            | Yes                               |
| Wattage Selectable        | No                                |
| Finish Family             | White                             |
| Amps                      | 1.700A                            |
| IOT Enabled               | No                                |
| Lens Finish               | Frosted                           |
| Lens Material             | Plastic                           |
| Lensed                    | Yes                               |
| Operating Position        | Universal                         |
| Power Factor              | >0.5                              |
| SDS Class                 | LED_Lamp                          |
| Indoor Outdoor            | Indoor and Outdoor                |
| Product Technology        | LED                               |
| Incandescent Equivalent   | 100W                              |

#### ELECTRICAL

|                     |                               |
|---------------------|-------------------------------|
| CCT (Kelvin Temp)   | 2700K/3000K/3500K/4000K/5000K |
| Dimmable            | Non-Dimmable                  |
| Hours Rated         | 15000                         |
| Beam Angle (degree) | 180                           |
| Color Temp          | Warm White to Natural Light   |
| CRI                 | 80+                           |
| Operating Frequency | 60Hz                          |
| Operating Temp      | -4F to +104F (-20C to +40C)   |
| Lumens              | 1600L                         |
| Volts               | 12V-24V/12V-34V               |
| Watts               | 15W                           |

#### PHYSICAL

|               |        |
|---------------|--------|
| Lamp Base     | Medium |
| Finish        | Frost  |
| Housing Color | White  |
| ANSI Base     | E26    |
| Lamp Type     | A19    |
| MOD Lamps     | 2.32   |
| MOL           | 4.61   |

#### ADDITIONAL INFO

|                            |         |
|----------------------------|---------|
| Warranty                   | 2-Years |
| Rated For Enclosed Fixture | No      |

#### FEATURES

|              |     |
|--------------|-----|
| Flicker Free | Yes |
|--------------|-----|

#### PACKAGING

|                |                |
|----------------|----------------|
| UPC            | 045923144103   |
| Case Cube      | 0.5896         |
| Case Height    | 11.18          |
| Case Length    | 11.02          |
| Case Quantity  | 24             |
| Case UPC       | 10045923144100 |
| Case Weight    | 4.59           |
| Case Width     | 8.27           |
| EA Cube        | 0.0157         |
| EA Height      | 4.72           |
| EA Length      | 2.4            |
| EA Quantity    | 1              |
| EA Weight      | 0.14           |
| EA Width       | 2.4            |
| Inner Cube     | 0.1153         |
| Inner Height   | 5.12           |
| Inner Length   | 7.6            |
| Inner Quantity | 6              |
| Inner UPC      | 20045923144107 |
| Inner Weight   | 0.97           |
| Inner Width    | 5.12           |
| Pack Type      | Color Box      |
| Web Length     | 4.61           |
| Web Width      | 2.32           |

#### COMPLIANCE

|                   |                |
|-------------------|----------------|
| ADA Compliant     | No             |
| CA Prop 65        | Lead           |
| Dark Sky Rated    | No             |
| FCC Compliant     | Yes            |
| IP Rating         | IP20           |
| Location Rating   | Damp           |
| NSF Approved      | No             |
| ROHS Compliant    | Yes            |
| Safety Listing    | Not Applicable |
| California Ban    | Non-Compliant  |
| Title 20          | No             |
| T24/JA8 Compliant | No             |
| US State Ban      | CA             |