SATCO | NUVO




Project / Job Name:

Location:

Fixture Type:

Notes:

**67-341** - Edge Lit Exit Sign; Chicago Approved; White Housing; 120-277V; 90 min Backup; Double Face; Surface Mounting

DAMP LOCATION · c UL us LISTED · FC · RoHS COMPLIANT · 50,000 HOURS · 120-277V

## GENERAL

| | |
|---|---|
| Company | SATCO |
| EA Height | 2.36 |
| EA Width | 10.24 |
| EA Length | 17.32 |
| Material | Steel |
| Fixture Type | Exit Sign |
| Includes | Canopy Kit |
| Product Notes | 90 minute discharge time; 24 Hour Recharge Time; surface, side and ceiling mounting |
| Status | Active |
| Style | Utility |
| Surge Protection | Built-in surge protection - 1KV |
| Total Harmonic Distortion | <130% |
| CCT Selectable | No |
| Wattage Selectable | No |
| Finish Family | White |
| Amps | 0.033-0.014A |
| Lens Finish | Frosted |
| Lens Material | Acrylic |
| Power Factor | >0.4 |
| SDS Class | Lithium_Ion_Battery |
| Indoor Outdoor | Indoor |
| Product Technology | LED |
| Battery Discharge Time Minutes | 90 |
| Serviceable Battery | Yes |
| Battery Indicator | No |
| Digital Display | No |
| Battery Operating Temp | +32F to +140F (0C to +60C) |

## ELECTRICAL

| | |
|---|---|
| Hours Rated | 50000 |
| Operating Frequency | 50/60Hz |
| Operating Temp | +41F to +113F (+5C to +45C) |
| Volts | 120V-277V |
| Watts | 4W |
| Connection | Hardwire |
| Charge Time | 24hr |
| Battery Chemistry | LiFePO4 |

## PHYSICAL

| | |
|---|---|
| Lamp Base | Integrated |
| Finish | Gloss White |
| ANSI Base | Integrated |
| Lamp Type | Integrated LED |
| Fixture Shape | Rectangle |
| Mounting Procedure | Universal |

## ADDITIONAL INFO

| | |
|---|---|
| Warranty | 2-Years |

## PACKAGING

| | |
|---|---|
| UPC | 045923415746 |
| Case Cube | 1.795 |
| Case Height | 8.07 |
| Case Length | 21.46 |
| Case Quantity | 6 |
| Case UPC | 10045923415743 |
| Case Weight | 25.58 |
| Case Width | 17.91 |
| EA Cube | 0.2422 |
| EA Height | 2.36 |
| EA Length | 17.32 |
| EA Quantity | 1 |
| EA Weight | 3.88 |
| EA Width | 10.24 |
| Pack Type | Kraft Box |
| Web Height | 11.54 |
| Web Length | 1.61 |
| Web Width | 14.06 |

## COMPLIANCE

| | |
|---|---|
| CA Prop 65 | Lead |
| Dark Sky Rated | No |
| FCC Compliant | Yes |
| IP Rating | IP40 |
| Location Rating | Damp |
| NSF Approved | No |
| ROHS Compliant | Yes |
| Safety Listing | cULus - Listed |
| California Ban | Non-Compliant |
| Energy Star Certified | No |
| Title 20 | No |
| T24/JA8 Compliant | No |
| US State Ban | CA |



© Satco Products, Inc.
All rights reserved 2026