



Dell Inspiron for Business



*Business-ready features in Dell
Inspiron notebooks*



Dell Inspiron Ready for Business Features



Security

Protect sensitive data with a hardware TPM security chip and log in quickly and securely with a fingerprint reader.



Support

Dell Support Assist detects and resolves issues proactively, while ProSupport offers 24/7 expert help. Extend coverage with the ProSupport 4-year Maximum Warranty for peace of mind against unexpected issues.



Manageability

With Autopilot and Microsoft Intune, streamline device setup by automating configuration and deployment, allowing your team to start working immediately with minimal IT.



Intelligent Software

Enhance system performance and security with Dell BIOS, while Dell Update ensures smooth operation by automatically updating critical fixes and drivers. Leverage Dell Optimizer's AI for application and power optimization, use Excalibur OS for OS recovery support, and simplify updates with Dell Command Update.



Hardware

Boost productivity with a 10-key numpad for quick data entry.



Configurability

Accelerate your workflow with Smart Select, which provides pre-selected device configurations that are ready to ship quickly, ensuring your team gets the right tools without delay.



Proven Reliability

Enjoy peace of mind with Dell's high standards including military-grade testing for added reliability and durability.



Operating System

Windows 11 Home simplifies everyday tasks with a user-friendly interface, while Windows 11 Pro enhances productivity with advanced security features and remote desktop access, perfect for managing your business efficiently.





Built with sustainable materials

Dell Inspiron notebooks are designed for sustainability with recycled materials including recycled steel, recycled copper, recycled aluminum and post-consumer recycled plastic in laptop components.¹ Most Inspiron notebooks contain up to 34% recycled plastic.² These devices also ship with 50% recycled cobalt in the battery³, an industry leading innovation for Dell.⁴ Select Inspiron notebooks ship with adapters designed with recycled plastic⁵ and an industry leading use of 50% recycled copper⁶ in the cable and 98% recycled aluminum in the heat sink.⁷



Low-impact packaging

New Inspiron notebooks ship in packaging that's made with up to 100% recycled or renewable materials.⁸



Imprinted logos to reduce waste

Imprinted logos or plastic-free logos are more durable and produce less manufacturing waste than traditional manufacturing process used to produce plastic badge logos.⁹



Environmental Certifications & Registrations

Meeting environmental standards demonstrates how our products adhere to energy-efficiency specifications and other extensive climate-related standards. Inspiron laptops and desktops have 8.0 Energy Star rating throughout the portfolio, 27 EPEAT Silver registered products, and 100% of the 2024 portfolio is EPEAT Silver registered with Climate+.

FEATURE	TECHNICAL SPECIFICATION	FEATURE	TECHNICAL SPECIFICATION
MODEL NUMBER	Inspiron 15 3530	MULTIMEDIA	2 tuned speakers Headset Jack* Integrated widescreen HD (720p) Webcam with Single Digital Microphone in plastic chassis <i>*3.5mm Headset jack functionality varies by model configuration. For best results, use Dell recommended audio accessories.</i>
PROCESSOR OPTIONS	13th Generation Intel® Core™ i3-1305U, 10 MB Cache, 5 Core, 6 Threads, 1.60 GHz to 4.50 GHz, 15 W (HW TPM) 13th Generation Intel® Core™ i5-1334U, 12 MB cache, 10 cores, 12 threads, 1.30 GHz to 4.60 GHz, 15 W (HW TPM) 13th Generation Intel® Core™ i7-1355U, 12 MB cache, 10 cores, 12 threads, 1.70 GHz to 5.0 GHz, 15 W (HW TPM) Intel® Processor N100 (6 MB cache, 4 cores, 0.8 GHz to 3.40 GHz, 6W) Intel® Core™ i3-N305 (6 MB cache, 8 cores, 1.80 GHz to 3.80 GHz, 15W)	CONNECTIVITY OPTIONS	Realtek RTL8821CE, Wi-Fi 5 Bluetooth Realtek RTL8852BE, Wi-Fi 6 Bluetooth
OPERATING SYSTEM	Windows 11 Home Windows 11 Home in S mode Windows 11 Pro Windows 11 Pro - Academic Ubuntu (for 13th Generation Intel® Core™ i3-1305U, i5-1334U, i7-1355U only)	BATTERY OPTIONS	3-cell, 41 Wh, lithium-polymer (integrated) 4-cell, 54 Wh, lithium-polymer (integrated)
GRAPHICS	Integrated: Intel® UHD Graphics, Intel® Iris® Xe Graphics	AC ADAPTER	65 W AC adapter, 4.5 mm barrel
DISPLAY	15.6-inch, FHD, 1920 x 1080, 120 Hz, anti-glare, non-touch, 45% NTSC, 250 nits, wide-viewing angle, IPS 15.6-inch, FHD, 1920 x 1080, 60 Hz, anti-glare, touch, 45% NTSC, 220 nits, wide-viewing angle, IPS	DIMENSIONS & WEIGHT	H/W/D: Plastic chassis 0.67" – 0.75" x 14.11" x 9.27" (16.96mm – 18.99mm x 358.50mm x 235.56mm) Starting weight: 3.57 lbs. (1.62 kgs) Aluminum chassis 0.61" – 0.69" x 14.11" x 9.25" (15.52mm – 17.50mm x 358.50mm x 234.90mm) Starting weight: 3.64 lbs. (1.65 kgs)
MEMORY OPTIONS	For Intel® Processor N100 & Intel® Core™ i3-N305 with non-Type-C® configuration: 4 GB, 1 x 4 GB, DDR4, 3200 MHz 8 GB, 1 x 8 GB, DDR4, 3200 MHz For 13th Generation Intel® Core™ i3-1305U, i5-1334U, and i7-1355U: 4 GB, 1 x 4 GB, DDR4, 2666 MHz with Type-C® data only, 8 GB, 1 x 8 GB, DDR4, 2666 MHz with Type-C® data only, 8 GB, 2 x 4 GB, DDR4, 2666 MHz with Type-C® data only, dual-channel 12 GB, 1 x 4 GB + 1 x 8 GB, DDR4, 2666 MHz with Type-C® data only, dual-channel 16 GB, 2 x 8 GB, DDR4, 2666 MHz with Type-C® data only, dual channel 16 GB, 1 x 16 GB, DDR4, 2666 MHz with Type-C® data only,	COLOR	Carbon Black Platinum silver paint Platinum silver aluminum
STORAGE OPTIONS	128GB/256GB/512GB/1TB/2TB M.2 PCIe NVMe SSD	SECURITY	Hardware TPM Fingerprint Reader with Windows Hello (Optional) Dell Support Assist for Home PCs
PORTS, SLOTS & CHASSIS	2 USB 3.2 Gen I Type-A ports (on systems configured Intel® Processor N100 & Intel® Core™ i3-N305 configuration) 1 USB 3.2 Gen I Type-A port + 1 USB 3.2 Gen I Type-C data only (on systems configured with plastic chassis and 13th Generation Intel® Core™ processors) 1 USB 3.2 Gen I Type-A port + 1 USB 3.2 Gen I Type-C full function (on systems configured with aluminum cover chassis) 1 USB 2.0 port 1 Headset jack 1 HDMI 1.4 port* 1 M.2 2230/2280 slot for solid-state drive 1 SD 3.0 card slot <i>*The maximum resolution supported over HDMI is 1920x1080 @60Hz. No 4K2K output</i>	SOFTWARE	Compatible with Absolute software Compatible with CrowdStrike software
INPUT	Full-size, spill-resistant keyboard with numeric keypad Optional backlit full-size, spill-resistant keyboard with numeric keypad Multi-touch gesture-enabled precision touchpad with integrated scrolling	PERIPHERAL ECOSYSTEM	Limited Hardware Warranty Optional 1-4 year Dell ProSupport contracts available (must purchase Windows 11 Pro)
OPTICAL DRIVE OPTIONS	No Optical Drive	REGULATORY & ENVIRONMENTAL COMPLIANCE	Windows Autopilot

FEATURE	TECHNICAL SPECIFICATION	FEATURE	TECHNICAL SPECIFICATION
MODEL NUMBER	Inspiron 15 3535	MULTIMEDIA	2 tuned speakers Headset Jack* Integrated widescreen HD (720p) Webcam with Single Digital Microphone in plastic chassis Integrated widescreen FHD (1080p) Webcam with Dual Digital Microphone in metal chassis *3.5mm Headset <i>jack functionality varies by model configuration. For best results, use Dell recommended audio accessories.</i>
PROCESSOR OPTIONS	AMD® Ryzen3™ 7320U, 5 MB cache, 4 core, 8 threads, 2.40 GHz to 4.10 GHz, 15 W (HW TPM) AMD® Ryzen3™ 7330U, 10 MB cache, 4 core, 8 threads, 2.30 GHz to 4.30 GHz, 15 W (HW TPM) AMD® Ryzen5™ 7520U, 6 MB cache, 4 core, 8 threads, 2.80 GHz to 4.3 GHz, 15 W (HW TPM) AMD® Ryzen5™ 7530U, 19 MB cache, 6 core, 12 threads, 2 GHz to 4.50 GHz, 15 W (HW TPM) AMD® Ryzen7™ 7730U, 20 MB cache, 8 core, 16 threads, 2 GHz to 4.50 GHz, 15 W (HW TPM) AMD® Athlon™ Gold 7220U, 4 MB cache, 2 core, 4 threads, 2.40 GHz to 3.70 GHz, 15 W (HW TPM)	CONNECTIVITY OPTIONS	Realtek RTL8821CE, Wi-Fi 5 Bluetooth Realtek RTL8852BE, Wi-Fi 6 Bluetooth
OPERATING SYSTEM	Windows 11 Home Windows 11 Home in S mode Windows 11 Pro Windows 11 Pro - Academic	BATTERY OPTIONS	3 cell, 41 Wh, lithium-polymer (integrated) 4 cell, 54 Wh, lithium-polymer (integrated)
GRAPHICS	Integrated: AMD Radeon Graphics	AC ADAPTER	65 W AC adapter, 4.5 mm barrel
DISPLAY	15.6-inch, FHD, 1920 x 1080, 120 Hz, anti-glare, non-touch, 45% NTSC, 250 nits, wide-viewing angle, IPS 15.6-inch, FHD, 1920 x 1080, 60 Hz, anti-glare, touch, 45% NTSC, 220 nits, wide-viewing angle, IPS	DIMENSIONS & WEIGHT	H/W/D: Plastic chassis 0.67" – 0.75" x 14.11" x 9.27" (16.96mm – 18.99mm x 358.50mm x 235.56mm) Starting weight: 3.59 lbs. (1.63 kgs)
MEMORY OPTIONS	For AMD® Ryzen3™ 7330U / Ryzen5™ 7530U / Ryzen7™ 7730U: 4 GB, 1 x 4 GB, DDR4, 3200 MHz 8 GB, 1 x 8 GB, DDR4, 3200 MHz 8 GB, 2 x 4 GB, DDR4, 3200 MHz, dual-channel 12 GB, 1 x 4 GB + 1 x 8 GB, DDR4, 3200 MHz, dual-channel 16 GB, 1 x 16 GB, DDR4, 3200 MHz 16 GB, 2 x 8 GB, DDR4, 3200 MHz, dual-channel For AMD® Athlon™ Gold 7220U / Ryzen3™ 7320U / Ryzen5™ 7520U: 8 GB, 1 x 8 GB, LPDDR5, 5500 MHz 8 GB, 1 x 8 GB, LPDDR5x, 5500 MHz	COLOR	Carbon Black Platinum silver paint
STORAGE OPTIONS	256GB/512GB/1TB/2 TB M.2 PCIe NVMe SSD	SECURITY	Hardware TPM Fingerprint Reader with Windows Hello (Optional) Dell Support Assist for Home PCs
PORTS, SLOTS & CHASSIS	1 USB 3.2 Gen1 Type-C port (data only) 1 USB 3.2 Gen1 Type-A port 1 USB 2.0 port 1 Headset jack 1 HDMI 1.4* 1 SD 3.0 card slot <i>*The maximum resolution supported over HDMI is 1920x1080 @60Hz. No 4K2K output.</i>	SOFTWARE	Compatible with Absolute software Compatible with CrowdStrike software
INPUT	Full-size, spill-resistant keyboard with numeric keypad Optional backlit full-size, spill-resistant keyboard with numeric keypad Multi-touch gesture-enabled precision touchpad with integrated scrolling	PERIPHERAL ECOSYSTEM	Limited Hardware Warranty Optional 1-4 year Dell ProSupport contracts available (must purchase Windows 11 Pro)
OPTICAL DRIVE OPTIONS	No Optical Drive	REGULATORY & ENVIRONMENTAL COMPLIANCE	Windows Autopilot

Business features compare

	Inspiron 3K & 5K Series	Latitude 3000 Series
Security		
Fingerprint Reader	✓	Optional
Hardware TPM	✓	✓
Lock Slot	14"/16" only	✓
Chassis Intrusion Switch		✓
Hard Drive Retention		✓
Services		
Accidental Damage Protection	✓	✓
Asset Recovery Services	✓	✓
Extended Battery Service	✓	✓
ProDeploy		✓
Support		
SupportAssist	✓	✓
ProSupport	✓	✓
ProSupport Max Warranty	4 yrs.	5 yrs.
Tech Direct		✓
Software		
Dell BIOS	✓	✓
Dell Optimizer	✓	✓
Excalibur (OS Recovery)	✓	✓
Dell Command Update (DCU)	✓	✓
Absolute	✓	✓
Crowdstrike	✓	✓
Dell Trusted Device		✓
Dell Command Configure (DCC)		✓
Dell Command Monitor (DCM)		✓
Dell Command Shell Provider (DCPP)		✓
Dell Command Endpoint Configure (DCEC) – Intune		✓
Dell Command Warranty (DCW)		✓
Dell Command Integration Suite (DCIS)		✓
Manageability		
Autopilot	✓	✓
Microsoft Intune	✓	✓

Business features compare (continued)

	Inspiron 3K & 5K Series	Latitude 3550
Operating System		
Windows 11 Home	✓	✓
Windows 11 Pro	✓	✓
Ubuntu		✓
National Academic K-12	✓	✓
Configurability		
Smart Select	✓	✓
Managed Transitions		✓
Customizable Configuration		✓
Custom Factory Install		✓
Non-Factory Services (CFS)		✓
Serviceability		
Serviceable by End Customer		✓
Serviceable by Field Technician	✓	✓
Hardware		
Numpad	✓	✓
MIL-STD-810H Tested	✓	✓
Metal Chassis	✓	
Camera Shutter	w/ Metal Chassis on 14"/16"	✓
RJ45 Ethernet Port	Dongle	✓
Mobile Broadband		

For a more detailed comparison, please visit this [Inspiron Consumer Features for Commercial chart](#).