Project / Job Name:

Location:

Fixture Type:

Notes:



S30104 - LED Foldable Task Light; 400 Max Lumens; USB-C Rechargeable; 3.7 Volt; 12pc Tray Pack

GENERAL

Company	SATCO
EA Height	9.0
EA Width	2.75
EA Length	2.25
Material	ABS Plastic
Fixture Type	Rechargeable Task
Includes	USB-A to USB-C Charging Cable
Product Notes	Integrated Rechargeable 3.7V Li-ion Battery; Charge Time: 3.5HRS
Status	Active
CCT Selectable	No
Wattage Selectable	No
Finish Family	Black
Additional Info	Ships in retail-ready display trays and packaging
Integrated Features	Magnetic Base; Hang Hook; Foldable
Lens Finish	Clear
Lens Material	Acrylonitrile Styrene (AS)
Lensed	Yes
Portable Light Modes	High, Low, Off
Product Technology	LED
Serviceable Battery	No
Beam Distance (Ft)	66
Battery Indicator	Yes
Digital Display	No
Drop Impact Rating	2.62 Ft (0.8M)
Battery Operating Temp	+32F to +104F (0C to +40C)
Light Source Quantity	Double
Power Bank Storage	1200mAh

ELECTRICAL

CCT (Kelvin Temp)	7000K
Dimmable	Yes-Dimmable
Color Temp	Daylight
CRI	50+
Dimming Type	Only dimmable via setting selection, Step Dimming
Operating Temp	+32F to +104F (0C to +40C)
Lumens	30L/400L/200L
Volts	3.7V
Max Lumens	400L
Connection	USB-C Rechargeable
Charge Time	3.5hr
Battery Chemistry	Lithium-ion (Li-ion)
Replaceable Battery Type	18650
USB Type In	1 USB-C

PHYSICAL

Finish	Black / Gray / Red
Housing Color	BlackGrayRed
Mounting Procedure	Hang Hook, Magnetic Base

ADDITIONAL INFO

Warranty	1-Year
Installation Notes	Do Not Charge The Product Below 40F Or above 104F; Do Not Exceed 5V DC, 1A Charging
Portable Light Functions	LED Spot Function

PACKAGING

UPC	045923300059
Case Cube	2.1725
Case Height	20.47
Case Length	10.24
Case Quantity	48
Case UPC	10045923300056
Case Weight	31.53
Case Width	17.91
EA Cube	0.0322
EA Height	9.0
EA Length	2.25
EA Quantity	1
EA Weight	0.46
EA Width	2.75
Inner Cube	0.4357
Inner Height	9.33
Inner Length	9.45
Inner Quantity	12
Inner UPC	20045923300053
Inner Weight	7.61
Inner Width	8.54
Pack Type	Color Box
Web Height	13.97
Web Length	2.3
Web Width	1.34

COMPLIANCE

CA Prop 65	Lead
FCC Compliant	Yes
IP Rating	IPX4
ROHS Compliant	Yes
Energy Star Certified	No
T24/JA8 Compliant	No
Performance Standards	ANSI PLATO FL1

© Satco Products, Inc.
All rights reserved 2026