



TEGERA® CHEMFORCE 7361

Learn more

2 PROTECTIONS IN ONE GLOVE

Chemical and heat protection 0,3* mm/11,8 mil glove with long safety cuffs and sandy finish for a perfect grip. Suitable for areas where there is a risk of thermal heat injuries. Comfortable lining and enhanced dexterity. Oil and grease resistant, water and oil repellent. With Oeko-Tex certificate.

CHARACTERISTICS

- Good fingertip sensitivity
- Flexible
- Excellent grip
- Excellent grip in oily environments

FUNCTIONS

- Withstands contact heat up to 100°C
- Phthalate-free
- Latex-free
- Oil and grease resistant
- Waterproof

OEKO TEX® STANDARD 100 SE 14-214 RISE

All values for the specified product are indicated without tolerances and may vary to actual value for individual products. We reserve the right to modify or update the information in this document without prior notice.

PREVENTS RISK OF

Risk of infection, Corrosive injuries, Puncturing, Contact with chemicals, Contact with moisture, Contact with damp, Contact with oil, Contact with oil and fat

PRIMARY ENVIRONMENTS OF USE

Chemical risk environments, Microbiological risk environments, Environments hazardous to health, Corrosive environments, Wet environments, Oily and greasy environments, Dirty environments, Harsh environments

PRIMARY AREAS OF USE

Mining, Repair work, Marine work, Fishing, Petro-chemical work, Chemical work, Chemical technology work, Laboratory work, Paper industry work, Decontamination, Sanitation, Cleaning

PRIMARY INDUSTRIES OF USE

Metal manufacturing and fabrication, Transport equipment manufacturing, Oil and gas extraction, Chemical and petrochemical industry, Basic metals manufacturing, Machinery and equipment manufacturing, Automotive manufacturing, Pulp and paper, Public safety, security and defence

CHEMICAL RESISTANCE

According to EN16523-1:2015. For details, please contact Ejendals.

SPECIFICATION

TYPE Chemical protection gloves, Heat protection gloves
CATEGORY Cat. III
COLLECTION Chemforce
THICKNESS 0,3* mm (*chem-layer)
LINING Fully lined
KNITTING GAUGE (GG) 18
LINING MATERIAL Nylon
LENGTH 340 mm
DEXTERITY 5
GRIP DESIGN Sandy finish
COLOUR Green
PAIRS PER: BUNDLE/CARTON 12/60
DISPLAY TYPE Bag with euro slot
DIPPING Fully dipped
DIPPING MATERIAL Nitrile

COMPLIANCE

CE 2777

UKCA 0321

EAC

TP TC 019:2011

EN ISO 21420:2020

EN 388:2016+A1:2018
4121X

EN 407:2020 (No flame protection)
X1XXXX

EN ISO 374-1:2016+A1:2018 Type A
AJKMNOPT

EN ISO 374-5:2016
Virus

NOT FOR FATTY FOOD

ANSI 5 ABR

FEATURES

Chemical protection

Waterproof

TEST ACCORDING TO EN ISO 374-1:2016

Tested chemical	A	J	K	M	N	O	P	T
Permeation level	2	5	6	2	2	3	6	6
Degradation %	50,8	9,7	-4.9	26,2	30,9	23,1	50,0	30,2

SIZE		ARTICLE NUMBER	EAN
7	S	7361-7	7340118325286
8	M	7361-8	7340118325309
9	L	7361-9	7340118325323
10	XL	7361-10	7340118325248
11	XXL	7361-11	7340118325262

ejendals
Limavägen 28, SE-793 32 Leksand, Sweden
Phone +46 (0) 247 360 00 | info@ejendals.com | order@ejendals.com

All values for the specified product are indicated without tolerances and may vary to actual value for individual products. We reserve the right to modify or update the information in this document without prior notice.