



Technical Data



Bouton® Optical Zenon Z13™ Rimless Safety Glasses with Clear Temple, I/O Lens and Anti-Scratch Coating

- Lightweight, rimless design provides all day user comfort
- Flexible, rubber tip temples provide a secure fit without uncomfortable pressure points
- Molded nose bridge design to fit the vast majority of users
- Variety of lenses available to fit your application
- 10 Base curve lens
- Meets ANSI Z87.1+
- Meets CSA Z94.3
- ⚠ **WARNING:** Reproductive Harm - www.P65Warnings.ca.gov

Color	Clear
Sizes Available	OS
Packaging	Bagged Each
Packed	144 Pair/Case
Case Dimensions (in)	25.59 x 10.63 x 12.60
Case Weight (lbs)	13.23
Country of Origin	Taiwan
Lens	Indoor Outdoor
Frame Style	Rimless
Lens Color	Clear
Frame Fit	Universal
Lens Coating	Anti-Scratch
Bridge	Molded
Temple	Rubber Tips
Base Curve	10
Certifications	ANSI Z87.1, CSA Z94.3 Certified, TAA Compliant
Product Circularity	Recycled via Terracycle

Applications

- Artificial Light
- Indoor/Outdoor Work
- Fork Lift Operation

KEY: Made from recycled or bio-based Launderable Recyclable via TerraCycle®

PIP GLOBAL SAFETY | PROTECTION EMPOWERED™

AMERICAS: +1 (800) 262-5755 | EUROPE: +34-96182-41-48 | AMEA: (ASIA, MIDDLE EAST, AFRICA) 852-2475-9228 | www.pipglobalsafety.com

This document and the information contained herein is the property of Protective Industrial Products, Inc. (PIP) and may not be used or reproduced without permission. Product users should conduct all appropriate testing or other evaluations to determine the suitability of PIP products for a particular purpose or use within a particular environment. PIP DISCLAIMS ALL WARRANTIES OTHER THAN AS EXPRESSLY PROVIDED. 2026-07-21

SKU Information

SKU	FRAME COLOR	LENS	LENS		UPC	UPC (INNER)	UPC (CASE)
			LENS COLOR	COATING			
250-06-0000	Clear	Clear	Clear	AS	616314036071	01616314036071	02616314036071
250-06-0002	Clear	I/O	Clear	AS	616314036255	01616314036255	02616314036255
250-06-0005	Black	Mirror	Silver	AS	616314049934	01616314049933	02616314049932
250-06-0006	Black	Mirror	Blue	AS	616314049927	01616314049926	02616314049925
250-06-0014	Black	IR Filter	Green	U	616314267284	01616314267283	02616314267282
250-06-0020	Clear	Clear	Clear	AS/AF	616314036262	01616314036262	02616314036262
250-06-0080	Clear	Clear	Clear	U	616314036309	01616314036309	02616314036309
250-06-5501	Dark Gray	Tinted	Gray	AS	616314022821	01616314022821	02616314022821
250-06-5503	Light Blue	Tinted	Light Blue	AS	616314036279	01616314036279	02616314036279
250-06-5504	Dark Brown	Tinted	Dark Brown	AS	616314036286	01616314036286	02616314036286
250-06-5509	Amber	Tinted	Amber	AS	616314036293	01616314036293	02616314036293
250-06-5521	Dark Gray	Tinted	Gray	AS/AF	616314067198	01616314067197	02616314067196

KEY: AF = Anti-Fog / AR = Anti-Reflective / AS = Anti-Scratch / FL360 = Fogless 3Sixty / U = Uncoated