

Garant**Insert, Ø Dmin: 8,9mm**

Order data

Order number	237625 8,9
GTIN	4045197681553
Item class	29W

Description

Application:

For micro-boring heads No. 237495 and No. 237498.

With adaptor allows inserts No. 237625.

Boring range Ø 6.9 – 19.1 mm.

Technical description

Boring range Ø	8.9 - 10.1 mm
Minimum Ø D _{min}	8.9 mm
maximum bore depth	30 mm
for type	D07
Type of product	Boring tool

