SCHAEFER

VKM24-2-O

VKM24-2-O



Product Description

Reduce heat stress and improve air quality with Schaefer's uniquely designed circulation fans. Unrivaled in the market, these fans are engineered to produce greater air movement and superior cooling no matter the application. You don't hear them. You don't see them. You only feel them!

Also known as Horizontal Air Flow (HAF) fans, these fans move air in a coherent horizontal pattern creating a gentle 'racetrack' air flow pattern needed in greenhouses to maximize heat distribution and humidity control by mixing the air, from ceiling to floor.

Features

Deep guard design for unmatched performance, low noise levels and safety without sacrificing airflow

Matched high quality motors and blades for maximum efficiency

Powder coated steel guards for increased durability and corrosion resistance

Hot dipped galvanized guards on VK12-GA and VK20-GA models for even greater rust protection

Powder coated steel mounting bracket and power cord included

Wide variety of mounting options available for flexible and easy installation

Variable speed controls available

Misting kits available for even greater cooling

Two year warranty

Made in the USA

Specifications

Blade Color	Metallic
Brand	Schaefer
Drive	Direct
Housing Material	Polyethylene
Phase	1
Speeds	2
Vfd Compatible	No
Cord	Included - Wired
Diameter (inches)	24
Frequency (hz)	60
Guard Color	White
Nameplate Amps	5.2

Number Of Wings	3
Power (hp)	1/2
Product Net Weight (lbs)	55
Switch	On product
Voltage	115
Maximum Rpm	1075
Blade Material	Aluminum
Cfm (high)	5640
Cfm Calculation Standard	ANSI/AMCA Standard 230-99
Product Color	White
Product Shipping Dimensions (in)	32 x 28 x 16
Speed Control Compatible?	No

Able To Ship Small Parcel	No
Cfm (low)	4580
Cfm Range (free Air)	5001 - 10000
Cord Length (feet)	5
Fixed Or Portable	Portable
Guard Material	Powder Coated Steel
Oscillating	No
Country Of Origin	US
Guard Spacing (inches)	1/2 OSHA
Housing Color	White

SIGN UP!