



Project / Job Name:

Location:

Fixture Type:

Notes:

S14318 - 8.5 Watt LED A19; 4000K CCT; Medium Base; Plastic; 120 Volt; 100-Pack



GENERAL

Company	SATCO
EA Height	11.25
EA Width	13.25
EA Length	23.5
Material	Plastic
Fixture Type	Miniature
Status	Active
Surge Protection	Built-in-surge protection - 0.5KV
Total Harmonic Distortion	<150%
CCT Selectable	No
Wattage Selectable	No
Finish Family	White
Amps	0.125A
IOT Enabled	No
Lens Finish	Frosted
Lens Material	Plastic
Lensed	Yes
Operating Position	Universal
Power Factor	>0.5
SDS Class	LED_Lamp
Indoor Outdoor	Indoor and Outdoor
Product Technology	LED
Incandescent Equivalent	60W

ELECTRICAL

CCT (Kelvin Temp)	4000K
Dimmable	Non-Dimmable
Hours Rated	15000
Beam Angle (degree)	180
Color Temp	Cool White
CRI	80+
Operating Frequency	60Hz
Operating Temp	-4F to +104F (-20C to +40C)
Lumens	800L
Volts	120v
Watts	8.5W

PHYSICAL

Lamp Base	Medium
Finish	Frost
Housing Color	White
ANSI Base	E26
Lamp Type	A19
MOD Lamps	2.28
MOL	3.98

ADDITIONAL INFO

Warranty	2-Years
Rated For Enclosed Fixture	Yes

FEATURES

Flicker Free	Yes
--------------	-----

PACKAGING

UPC	045923143182
Case Cube	2.0272
Case Height	11.25
Case Length	23.5
Case Quantity	1
Case UPC	10045923143189
Case Weight	7.68
Case Width	13.25
EA Cube	2.0272
EA Height	11.25
EA Length	23.5
EA Quantity	1
EA Weight	7.68
EA Width	13.25
Pack Type	Color Box
Web Length	3.98
Web Width	2.28

COMPLIANCE

CA Prop 65	Lead
Dark Sky Rated	No
FCC Compliant	Yes
IP Rating	IP20
Location Rating	Damp
NSF Approved	No
ROHS Compliant	Yes
Safety Listing	cETLus - Listed
California Ban	Non-Compliant
Title 20	No
T24/JA8 Compliant	No
US State Ban	CA