



<b>EAN:</b>	4013288156952	<b>Size:</b>	50x7x6 mm
<b>Part number:</b>	05134656001	<b>Weight:</b>	11 g
<b>Article number:</b>	867/4 IPR	<b>Country of origin:</b>	CZ
		<b>Customs tariff number:</b>	82079030

- For recessed TORX PLUS® IPR screws with safety pin
- TORX PLUS® IPR bit with bore hole on the output side
- Tough for hard materials
- 1/4" hexagon drive (Wera connecting series 4)

High quality bits for recessed TORX PLUS® screws with safety pin. A 5-flank TORX PLUS® profile with bore hole. 1/4" hexagon, suitable for holders as per DIN ISO 1173-F 6.3.

**Web link**  
<https://www.wera.de/en/05134656001>

Wera - 867/4 IPR  
05134656001 - 4013288156952

Wera Werkzeuge GmbH  
Korzter Straße 21-25  
D-42349 Wuppertal  
Tel: +49 (0)2 02 / 40 45-0  
E-Mail: [info@wera.de](mailto:info@wera.de)

For recessed TORX PLUS® IPR screws with safety pin





Tough bits



A 5-flank TORX PLUS® profile with a borehole. This drive geometry has only five flanks instead of the usual six and a borehole to protect safety screws against unauthorised unfastening. The screws cannot be turned with conventional, widely available tools.

Tough Wera bits prevent the tip from breaking prematurely. Z-bits usually are the bit for universal screwdriving applications.

Further versions in this product family:

		 mm	 inch	 mm
05160821001	10 IPR	50	2"	4.0
05134657001	10 IPR	89	3 1/2"	4.0
05134654001	15 IPR	50	2"	4.0
05134720001	15 IPR	89	3 1/2"	4.0
05204126001	20 IPR	50	2"	4.5
05259135001	20 IPR	89	3 1/2"	4.5
05134655001	25 IPR	50	2"	6.0
05134722001	25 IPR	89	3 1/2"	6.0
<b>05134656001</b>	<b>27 IPR</b>	<b>50</b>	<b>2"</b>	<b>6.0</b>
05134658001	27 IPR	89	3 1/2"	6.0
05134732001	30 IPR	50	2"	6.0
05134723001	30 IPR	89	3 1/2"	6.0

**Web link**

<https://www.wera.de/en/05134656001>

Wera - 867/4 IPR

05134656001 - 4013288156952

Wera Werkzeuge GmbH

Korzter Straße 21-25

D-42349 Wuppertal

Tel: +49 (0)2 02 / 40 45-0

E-Mail: [info@wera.de](mailto:info@wera.de)