



Project / Job Name: _____

Location: _____

Fixture Type: _____

Notes: _____

TH674 - Orb; 12 Watt LED H-Style Track Head; 3000K/4000K/5000K CCT Selectable; 36 Degree Beam Angle; Black Finish; 120 Volt; H-Style



GENERAL

| | |
|---------------------------|---------------------------------|
| Company | SATCO |
| EA Height | 1.73 |
| EA Width | 5.4 |
| EA Length | 7.87 |
| Bulb Included | Integrated |
| Diameter | 4.7 |
| Dimmable Text | Forward Phase; Linear Dimming |
| Material | Aluminum |
| Fixture Type | Track Head |
| Status | Active |
| Style | Contemporary |
| Surge Protection | Built-in surge protection - 2KV |
| Total Harmonic Distortion | <40% |
| Track Head Style | Circle |
| Up Down Installation | Universal |
| CCT Selectable | Yes |
| Wattage Selectable | No |
| Collection | Orb |
| Finish Family | Black |
| Amps | 0.120A |
| Lens Material | Poly methyl methacrylate (PMMA) |
| Power Factor | 0.9 |
| SDS Class | LED_Fixture |
| Sloped Ceiling Compatible | Yes |
| Indoor Outdoor | Indoor |
| Product Technology | LED |
| Incandescent Equivalent | 75W |

ELECTRICAL

| | |
|---------------------|-----------------------------|
| CCT (Kelvin Temp) | 3000K/4000K/5000K |
| Dimmable | Yes-Dimmable |
| Hours Rated | 50000 |
| Beam Angle (degree) | 36 |
| Color Temp | Soft White to Natural Light |
| CRI | 90+ |
| Dimming Type | Linear Dimming, Phase cut |
| Operating Frequency | 60Hz |
| Operating Temp | -20C (-4F) to +40C (+104F) |
| Lumens | 1020L |
| Volts | 120v |
| Watts | 12W |

PHYSICAL

| | |
|---------------|----------------|
| Lamp Base | Integrated |
| Finish | BLACK |
| Housing Color | Black |
| ANSI Base | Integrated |
| Lamp Type | Integrated LED |
| Fixture Shape | Round |

ADDITIONAL INFO

| | |
|----------|---------|
| Warranty | 3-Years |
|----------|---------|

PACKAGING

| | |
|---------------|----------------|
| UPC | 045923412110 |
| Case Cube | 0.6517 |
| Case Height | 8.66 |
| Case Length | 11.61 |
| Case Quantity | 12 |
| Case UPC | 10045923412117 |
| Case Weight | 12.05 |
| Case Width | 11.2 |
| EA Cube | 0.0425 |
| EA Height | 1.73 |
| EA Length | 7.87 |
| EA Quantity | 1 |
| EA Weight | 0.92 |
| EA Width | 5.4 |
| Pack Type | Kraft Box |
| Web Height | 7.13 |
| Web Length | 5.63 |
| Web Width | 1.3 |

COMPLIANCE

| | |
|-----------------|-----------------|
| CA Prop 65 | Lead |
| Dark Sky Rated | No |
| FCC Compliant | Yes |
| IP Rating | IP20 |
| Location Rating | Dry |
| NSF Approved | No |
| ROHS Compliant | Yes |
| Safety Listing | cETLus |
| California Ban | Lawful for sale |
| Title 20 | Exempt |
| T24 Compliant | Yes |