



Post Office Box 97
Benton Harbor, Michigan
Ph: 616/926-6171
Fax: 616/925-8288

PART NUMBER:

LTD106

REV.

D

Product Specifications

Model Number	MAX. PRESS.		MAX. SPEED	HP	kW	Net Wt.	
	bar.	PSI				lbs.	kg
8AM-NRV-28A	7.0	100	2,500 RPM	5.0	4.0	28	12,7
8AM-NRV-32A	7.0	100	2,500 RPM	5.0	4.0	28	12,7

SOUND LEVEL 105 dba MAX.

NORMAL AMBIENT +1°C. - 120°C.

RELATIVE HUMIDITY 0% - 100%

ENVIRONMENT HAZARDOUS AMBIENT COMBUSTIBLE
GAS AND DUST +1°C TO +40°C

* TECHNICAL DATA SUBJECT TO CHANGE
WITHOUT NOTICE.

CONFORMS TO EUROPEAN STANDARD EN13463-1
NON ELECTRICAL EQUIPMENT FOR EXPLOSIVE
ATMOSPHERES GROUP II, CAT 2 (GAS AND DUST)
PROTECTED BY CONSTRUCTION
(SURFACE TEMP RATED 135±C)

