



EAN:	4013288032379	Size:	157x13x13 mm
Part number:	05118124001	Weight:	19 g
Article number:	2069 Micro	Country of origin:	CZ
		Customs tariff number:	82054000

- Kraftform Micro nutsetter for hex head screws
- Multi-component Kraftform Micro handle for fast and ergonomic screwdriving
- Take it easy tool finder: colour coding according to profile and size
- Anti-roll feature and rotating cap for rapid twisting
- E.g. for electricians, opticians, precision mechanics, jewellers or IT hardware fitters

Premium Wera Micro insert wrench for precision mechanical couplings. By supporting the hand on the rotating cap, and due to the fast rotating zone below the rotating cap, lightning fast turning is possible. Time-consuming hand switching is eliminated. The power zone with integrated soft zones ensures the transmission of high tightening and loosening moments. Precision zone for correct rotation angles whilst adjusting. Take it easy tool finder with size stamping and colour coding by profile for quick and easy identification of the required tool.



Web link
<https://www.wera.de/en/05118124001>

Wera - 2069 Micro
 05118124001 - 4013288032379

Wera Werkzeuge GmbH
 Korzter Straße 21-25
 D-42349 Wuppertal
 Tel: +49 (0)2 02 / 40 45-0
 E-Mail: info@wera.de

Kraftform Micro handle



Screwdriving jobs in electrical and precision engineering applications are often tedious and time-consuming. We learned from users what is important for them: working speeds, torque, precision - and we then focused particularly on these issues.



Multi-component screwdriver handle for ergonomic working.

The refined screwdriver for electronics technicians



The Kraftform Micro, with its three zones and their specific arrangement, satisfies these requirements perfectly. The free-turning cap that provides support for the hand works with these advantages, enabling quick and easy precision work.

The precision zone




The precision zone directly above the blade gives the user a better feel for the right rotation angle during fine adjustment work.

The power zone




The power zone has integrated soft zones near the blade tip to ensure high torque transfer for loosening or tightening screws without losing contact with the screw.

The fast-turning zone



The fast-turning zone just below the rotating cap allows rapid spinning.

Take it easy Tool Finder



Screwdrivers with Take it easy tool finder: colour coding according to profile and size stamp.

Applications









Indispensable for many users, including electronics technicians, opticians, precision engineers, jewellers, EDP hardware fitters and model-makers

Web link
<https://www.wera.de/en/05118124001>

Wera - 2069 Micro
 05118124001 - 4013288032379

Wera Werkzeuge GmbH
 Korzter Straße 21-25
 D-42349 Wuppertal
 Tel: +49 (0)2 02 / 40 45-0
 E-Mail: info@wera.de

Further versions in this product family:

						
	mm	inch	mm	mm	mm	inch
05118108001	1.5	-	60	97	5.7	2 3/8"
05118109001	1.8	-	60	97	5.7	2 3/8"
05118110001	2.0	-	60	97	5.7	2 3/8"
05118112001	2.5	-	60	97	5.7	2 3/8"
05118114001	3.0	-	60	97	5.7	2 3/8"
05118116001	3.2	-	60	97	5.7	2 3/8"
05118118001	3.5	-	60	97	5.7	2 3/8"
05118120001	4.0	-	60	97	5.7	2 3/8"
05118122001	4.5	-	60	97	6.4	2 3/8"
05118124001	5.0	-	60	97	7.0	2 3/8"
05118126001	5.5	-	60	97	7.8	2 3/8"
05345281001	6.0	-	60	97	8.5	2 3/8"
05118128001	-	3/32"	60	97	5.7	2 3/8"
05118130001	-	7/64"	60	97	5.7	2 3/8"
05118132001	-	1/8"	60	97	5.7	2 3/8"
05118134001	-	9/64"	60	97	5.7	2 3/8"
05118136001	-	5/32"	60	97	5.7	2 3/8"
05118135001	-	3/16"	60	97	6.6	2 3/8"
05118137001	-	7/32"	60	97	7.8	2 3/8"
05345282001	-	1/4"	60	97	9.0	2 3/8"

Web link

<https://www.wera.de/en/05118124001>

Wera - 2069 Micro

05118124001 - 4013288032379

Wera Werkzeuge GmbH

Korzter Straße 21-25

D-42349 Wuppertal

Tel: +49 (0)2 02 / 40 45-0

E-Mail: info@wera.de