Berliner | E34002-BK

Job Name:_____ Job Type:_____ Quantity:_____ Comments:_____








PRODUCT DESCRIPTION

Wide flat discs house LED engines that disappear when viewed at the pendants edge. Supported at their center by thin tubes and black cable, machined aluminum housings feature laterally cut concentric circles drawing inspiration from the grooves in a vinyl record. Finished in your choice of Matte Black, Antique Brass, or Antique Copper, the modern design feels vintage and retro widening the range of compatibility within architectural aesthetics.



*max overall height

MEASUREMENTS

DIMENSION	: 19.75" W x 1.5" H x 19.75" Ext
MAX OAH	: 132" OAH
CANOPY	: 4.75" W x 0.25" H x 4.75" L
HANGING WEIGHT	: 2 lb

LAMPING

INPUT VOLTAGE	: 120V
LUMENS	: 1,080 Rated (860 Del.)
BULB	: 1 x 12W LED AC Integrated , 12W Total
BULB INCLUDED	: (Integrated)
DIMMABLE	: Triac or ELV
CRI	: 90 CRI
COLOR_TEMP	: 3000K

FINISHES OPTION

- Antique Brass (AB)
- Antique Copper (ACP)
- Black (BK)

MATERIAL

Steel

RATINGS

cETLus
Dry Location

ADDITIONAL

RATED LIFE 50000 Hours
OPERATING TEMPERATURE:
-20°C (-4°F), 40°C (104°F)

Always consult a qualified electrician before installing any lighting product.

ET2 Contemporary Lighting™

WESTERN DISTRIBUTION CENTER (HEADQUARTER)
253 NORTH VINELAND AVE I CITY OF INDUSTRY, CA 91746

EASTERN DISTRIBUTION CENTER
101 GARDNER PARK | PEACHTREE CITY, GA 30269

P. 626.956.4200 I F. 626.956.4225 I maximlighting.com