Citadel | E30314-BK

Job Name:_____ Job Type:_____ Quantity:_____ Comments:_____








PRODUCT DESCRIPTION

Vertical aluminum strands surround an acrylic LED tube that shines omnidirectional light filtered by the frame. The thin profile of the overall column extends less than 4" offering ADA compliant applications. Available in a variety of sconce sizes, the design is finished in a matte Black finish that complements most settings.



*Height from center of outlet to the top of the fixture

MEASUREMENTS

DIMENSION	: 3.25" L x 3.25" W x 15" H x 5" Ext
BACK PLATE	: 5" W x 5" H x 12.5" HCO
HANGING WEIGHT	: 1.6 lb

LAMPING

INPUT VOLTAGE	: 120-277V
LUMENS	: 1,000 Rated (600 Del.)
BULB	: 1 x 11W LED DC Integrated , 11W Total
BULB INCLUDED	: (Integrated)
DIMMABLE	: 3-in-1: Triac, ELV, or 0-10V
CRI	: 90 CRI
COLOR_TEMP	: 3000K
LIGHTING_DIRECTION	: Omni

FINISHES OPTION

Black (BK)

MATERIAL

Aluminum, Glass

RATINGS

cETLus
Wet Location

ADDITIONAL

INSTALL UP/DOWN: Vertical/Horizo
RATED LIFE 50000 Hours
OPERATING TEMPERATURE:
-20°C (-4°F), 40°C (104°F)

Always consult a qualified electrician before installing any lighting product.

ET2 Contemporary Lighting™

WESTERN DISTRIBUTION CENTER (HEADQUARTER)
253 NORTH VINELAND AVE I CITY OF INDUSTRY, CA 91746

EASTERN DISTRIBUTION CENTER
101 GARDNER PARK | PEACHTREE CITY, GA 30269

P. 626.956.4200 I F. 626.956.4225 I maximlighting.com