

# HOM120C

Mini circuit breaker, Homeline, 20A, 1 pole, 120/240VAC, 10kA AIR, standard type, plug in, UL



## Main

Product	Miniature circuit-breaker
Range	Homeline
Current Rating	20 A
Certifications	UL Listed
Voltage Rating	120/240 V AC
Mounting Type	Plug-in
Number of Poles	1P
Short Circuit Current Rating	10 kA
Number of Spaces	1
Circuit Breaker Type	Standard
Ratings	HACR and Switching Duty rated
Electrical Connection	Clamp terminal for 2 cables
Wire Size	AWG 14...AWG 8 aluminium/copper)1 AWG 14...AWG 10 copper)2
Type of Packing	Clam packaging

## Complementary

Tightening torque	35.40 lbf.in (4.0 N.m) 0.00...0.01 in <sup>2</sup> (2.5...6 mm <sup>2</sup> ) (AWG 14...AWG 8)
Height	3.13 in (79.50 mm)
Width	1 in (25.40 mm)
Depth	2.98 in (75.69 mm)

## Environment

Ambient Air Temperature for Operation	104 °F (40 °C)
---------------------------------------	----------------

## Ordering and shipping details

Category	01320-HOMELINE 1 POLE CRD.BRKR
Discount Schedule	CPH
GTIN	047569062889
Returnability	Yes
Country of origin	US

## Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	1.20 in (3.048 cm)
Package 1 Width	4.30 in (10.922 cm)
Package 1 Length	4.40 in (11.176 cm)
Package 1 Weight	5.12 oz (145.15 g)
Unit Type of Package 2	CAR
Number of Units in Package 2	6
Package 2 Height	5.20 in (13.208 cm)
Package 2 Width	4.80 in (12.192 cm)
Package 2 Length	6.60 in (16.764 cm)

Package 2 Weight	34.24 oz (970.687 g)
Unit Type of Package 3	PAL
Number of Units in Package 3	2304
Package 3 Height	40.00 in (101.6 cm)
Package 3 Width	40.00 in (101.6 cm)
Package 3 Length	48.00 in (121.92 cm)
Package 3 Weight	822.00 lb(US) (372.853 kg)

### Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	<a href="#">REACH Declaration</a>
REACH free of SVHC	Yes
EU RoHS Directive	Compliant <a href="#">EU RoHS Declaration</a>
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	<a href="#">Yes</a>
China RoHS Regulation	<a href="#">China RoHS Declaration</a>
Environmental Disclosure	<a href="#">Product Environmental Profile</a>

### Contractual warranty

Warranty	Lifetime
----------	----------