| REVISION HISTORY | | | |
|---|---|---|---|
| REV | DATE | BY | DESCRIPTION |
| L | 12DEC2023 | JD/VK | PRN:P2023-2310 |

## ASSEMBLY PART NUMBER

MP-07-WWV-YZ-P

FLANGE STYLE — HOOK IMAGE — HOOK FINISH — FLANGE FINISH — PANEL THICKNESS

FLANGE STYLE (WW)
- 11 - OVAL PERPENDICULAR
- 12 - OVAL IN-LINE
- 21 - SQUARE
- 31- ROUND


HOOK IMAGE (V)
- 2 - HANGER
- 3 - NONE
- 4 - HEADSET

FLANGE FINISH (Y)


HOOK FINISH (Z)
- 1 - POLISHED CHROME
- 2 - SATIN CHROME
- 3 - BRUSHED NICKEL
- 5 - BLACK POWDER COAT (FOR IMAGE STYLE 3 - BLANK ONLY)

PANEL THICKNESS (P)


| | | |
|---|---|---|
| OMIT- | MOUNTING NUT | 4-25.4 [0.16-1.01] |
| 0 - | SNAP-IN | 1.1-2.9 [0.043-.114] |
| 1 - | SNAP-IN | 2.9-5.3 [.114-.209] |
| 2 - | SNAP-IN | 5.3-7.0 [.209-.276] |





## SNAP IN






## FLANGE STYLE (WW):




## MOUNTING NUT




| COAT HOOK ASSEMBLY | - | - |
|---|---|---|
| HOOK | DIE CAST ZINC | SEE TABLE (Z) |
| RACHET | ACETAL | BLACK |
| RACHET SPRING | STAINLESS STEEL | PASSIVATED |
| SHAFT | STAINLESS STEEL | PASSIVATED |
| FLANGE | DIE CAST ZINC | SEE TABLE (Y) |
| HOOK SPRING | STAINLESS STEEL | PASSIVATED |
| HOUSING | GF NYLON | BLACK |
| GASKET | NEOPRENE | BLACK |
| LOCKWASHER | STAINLESS STEEL | PASSIVATED |
| MOUNTING NUT | GF NYLON | BLACK |
| COMPONENT | MATERIAL | FINISH |

PROPRIETARY ITEM
EXCEPT FOR USES EXPRESSLY GRANTED IN WRITING, INFORMATION DISCLOSED HEREON IS CONFIDENTIAL AND ALL RIGHTS, PATENT AND OTHERWISE, ARE RESERVED BY SOUTHCO, INC.

THIRD ANGLE PROJECTION

MILLIMETERS [IN]

TOLERANCES UNLESS OTHERWISE NOTED

ALL DIMENSIONS WITHOUT TOLERANCES ARE FOR REFERENCE ONLY.

PER ASME Y14.5M-2009

southco®
CONNECT·CREATE·INNOVATE

DESCRIPTION: MP EXTENDABLE COAT/HEADSET HOOK

| SIZE | SYSTEM | DWG NO. |
|---|---|---|
| A3 | NX | J-MP-07-1 |

| DRAWN BY | DATE | SCALE | SHEET |
|---|---|---|---|
| ACH/TL | 19MAY2009 | DNS | 1 OF 1 |