
Axle | E11041-24GLD

Job Name:_____ Job Type:_____ Quantity:_____ Comments:_____



PRODUCT DESCRIPTION

Suspended by an axle of Gold pins, a Clear glass orb is illuminated with a sleek continuing line of evenly diffused LED in a white acrylic cylinder. The elongated nature of the Gold metalwork is elegantly vertical in size with a pop of playful interest and light.



MEASUREMENTS

DIMENSION	: 8" W x 15.75" H x 9" Ext
MAX OAH	: 6" W x 14.5" H
HANGING WEIGHT	: 7.8 lb

LAMPING

INPUT VOLTAGE	: 120V
LUMENS	: 900 Rated (720 Del.)
BULB	: 1 x 10W LED PCB Integrated , 10W Total
BULB INCLUDED	: (Integrated)
DIMMABLE	: Triac
CRI	: 90 CRI
COLOR_TEMP	: 3000K
LIGHTING_DIRECTION	: Omni

FINISHES OPTION

Gold (GLD)

GLASS

Clear 24

MATERIAL

Aluminum

RATINGS

cETLus
Damp Location

ADDITIONAL

INSTALL UP/DOWN: Up
RATED LIFE 25000 Hours
OPERATING TEMPERATURE:
-20°C (-4°F), 40°C (104°F)

Always consult a qualified electrician before installing any lighting product.

ET2 Contemporary Lighting™

WESTERN DISTRIBUTION CENTER (HEADQUARTER)
253 NORTH VINELAND AVE I CITY OF INDUSTRY, CA 91746

EASTERN DISTRIBUTION CENTER
101 GARDNER PARK | PEACHTREE CITY, GA 30269

P. 626.956.4200 I F. 626.956.4225 I maximlighting.com