



Project / Job Name: \_\_\_\_\_

Location: \_\_\_\_\_

Fixture Type: \_\_\_\_\_

Notes: \_\_\_\_\_

**S16513** - 6 Watt T5 LED; 12 Inch; 35K/4K/5K/65K; G5 Base; Type A; Omni



**GENERAL**

Company	SATCO
EA Height	0.75
EA Width	0.75
EA Length	12.01
Lamp Ballast Type AB	Type A
Ballasting Requirements	Ballast required, check compatibility
Material	Polycarbonate (PC)
Fixture Type	Miniature
Status	Active
Total Harmonic Distortion	Ballast Dependent
CCT Selectable	Yes
Wattage Selectable	No
Finish Family	White
Amps	Ballast Dependent
Lens Finish	Frost
Lens Material	Glass
Nominal Length	12.0
Operating Position	Universal
Power Factor	Ballast Dependent
SDS Class	LED_Lamp
Shatter Proof Type	PET Coated
Indoor Outdoor	Indoor
Product Technology	LED
Fluor Equiv	8W

**ELECTRICAL**

CCT (Kelvin Temp)	3500K/4000K/5000K/6500K
Hours Rated	36000
Beam Angle (degree)	180
Color Temp	Neutral White to Daylight
CRI	80+
Operating Frequency	50/60Hz
Operating Temp	-4F to +113F (-20C to +45C)
Lumens	700L
Volts	Ballast Dependent
Watts	6W

**PHYSICAL**

Lamp Base	Miniature Bi Pin
Finish	Frost
ANSI Base	G5
Lamp Type	T5
MOD Lamps	0.62
MOL	11.91

**ADDITIONAL INFO**

Warranty	3-Years
Rated For Enclosed Fixture	Yes

**PACKAGING**

UPC	045923165139
Case Cube	0.1653
Case Height	4.72
Case Length	13.98
Case Quantity	25
Case UPC	10045923165136
Case Weight	2.55
Case Width	4.33
EA Cube	0.0039
EA Height	0.75
EA Length	12.01
EA Quantity	1
EA Weight	0.09
EA Width	0.75
Pack Type	Sleeve
Web Length	11.91
Web Width	0.62

**COMPLIANCE**

Dark Sky Rated	No
FCC Compliant	Yes
IP Rating	IP20
Location Rating	Damp
NSF Approved	No
ROHS Compliant	Yes
Safety Listing	cETLus - Listed
California Ban	Lawful for sale
Title 20	Exempt
T24/JA8 Compliant	No