Project / Job Name:

Location:

Fixture Type:

Notes:

62-1200 - LED Landscape Flood 6W; Bronze Finish; 3000K



GENERAL

Company	NUVO
EA Height	3.07
EA Width	3.54
EA Length	6.02
Bulb Included	Integrated
Diameter	2.45
Material	Die-cast Aluminum
Fixture Type	Flood Light
Status	Active
Style	Utility
CCT Selectable	No
Wattage Selectable	No
Finish Family	Bronze
Amps	0.050A
Has Camera	No
IOT Enabled	No
Photo Cell	No Photocell
SDS Class	LED_Fixture
Indoor Outdoor	Outdoor
Product Technology	LED
Incandescent Equivalent	45W
Serviceable Battery	No
Battery Indicator	No
Digital Display	No

ELECTRICAL

CCT (Kelvin Temp)	3000K
Dimmable	Non-Dimmable
Hours Rated	50000
Beam Angle (degree)	60
Color Temp	Warm White
CRI	80+
Operating Frequency	60Hz
Operating Temp	-4F to +104F (-20C to +40C)
Lumens	640L
Volts	120v
Watts	6W
Connection	Hardwire

PHYSICAL

Lamp Base	Integrated
Finish	BRONZE
ANSI Base	Integrated
Lamp Type	PAR16
Mounting Procedure	Pole/Post/Plate

ADDITIONAL INFO

Warranty	5-Years

PACKAGING

UPC	045923680168
Case Cube	0.5318
Case Height	7.48
Case Length	18.9
Case Quantity	12
Case UPC	10045923680165
Case Weight	10.05
Case Width	6.5
EA Cube	0.0379
EA Height	3.07
EA Length	6.02
EA Quantity	1
EA Weight	0.77
EA Width	3.54
Pack Type	Box
Web Height	3.25
Web Length	5.5
Web Width	2.45

COMPLIANCE

CA Prop 65	Lead
FCC Compliant	Yes
Location Rating	Wet
ROHS Compliant	Yes
Safety Listing	cULus
California Ban	Lawful for sale
UL Application	Landscape
DLC Approved	No
Title 20	Exempt
T24/JA8 Compliant	No

© Satco Products, Inc.
All rights reserved 2026