Stillo | E24217-122SN

Job Name:_____ Job Type:_____ Quantity:_____ Comments:_____








PRODUCT DESCRIPTION

The classic teardrop glass shade is elevated in a luxurious collection of pendant configurations using substantially dense glass that are hand blown in elongated forms and curated into various color combinations. Suspended within the long, slender glass is a similarly long and slender socket to illuminate an energy efficient LED G4 lamp at the base of the glass. The slender tube running within the glass also supports the glass with elegantly flat thumb screws in coordinating finishes. Choose from Matte Black metal with Mirror Smoked glass for a moodier ambience, crystal Clear glass that accentuates the thickness of the glass walls paired with transitional Satin Nickel metalwork, or celebrate the design with effervescent Bubble glass and plated Gold metalwork.



MEASUREMENTS

DIMENSION	: 17" L x 17" W x 18" H
MAX OAH	: 137.5" OAH
CANOPY	: 17" W x 1.5" H x 17" L
HANGING WEIGHT	: 23.34 lb

LAMPING

LUMENS	: 1,800 Rated (1,350 Del.)
BULB	: 9 x 1.5W LED G4 , 14W Total
BULB INCLUDED	: (Included)
CRI	: 90 CRI
COLOR_TEMP	: 3000K

FINISHES OPTION

- Black (BK)
- Gold (GLD)
- Satin Nickel (SN)

GLASS

Clear Crystal 122

MATERIAL

Glass, Steel

RATINGS

Dry Location

ADDITIONAL

OPERATING TEMPERATURE:
-20°C (-4°F), 40°C (104°F)

Always consult a qualified electrician before installing any lighting product.

ET2 Contemporary Lighting™

WESTERN DISTRIBUTION CENTER (HEADQUARTER)
253 NORTH VINELAND AVE I CITY OF INDUSTRY, CA 91746

EASTERN DISTRIBUTION CENTER
101 GARDNER PARK | PEACHTREE CITY, GA 30269

P. 626.956.4200 I F. 626.956.4225 I maximlighting.com