SATCO | NUVO



Project / Job Name:

Location:

Fixture Type:

Notes:

67-301 - Exit Sign; Chicago Approved; White Housing; 120-277V; 90 min Backup; Single Face; Surface Mounting; Remote Capable

DAMP LOCATION · c UL us LISTED · FC · RoHS COMPLIANT · 50,000 HOURS · 120-277V

GENERAL

Company	SATCO
EA Height	2.83
EA Width	10.04
EA Length	13.39
Material	Steel
Fixture Type	Exit Sign
Includes	Canopy Kit
Product Notes	90 minute discharge time; 24 Hour Recharge Time; wall, side or ceiling mounting
Status	Active
Style	Utility
Surge Protection	Built-in surge protection - 1KV
Total Harmonic Distortion	<130%
CCT Selectable	No
Wattage Selectable	No
Finish Family	White
Amps	0.054-0.023A
Lens Finish	Frosted
Lens Material	Glass
Power Factor	>0.4
SDS Class	Lithium_Ion_Battery
Indoor Outdoor	Indoor
Product Technology	LED
Battery Discharge Time Minutes	90
Serviceable Battery	Yes
Battery Indicator	No
Digital Display	No
Battery Operating Temp	+32F to +140F (0C to +60C)

ELECTRICAL

Hours Rated	50000
Operating Frequency	50/60Hz
Operating Temp	+41F to +113F (+5C to +45C)
Volts	120V-277V
Watts	6.5W
Connection	Hardwire
Charge Time	24hr
Battery Chemistry	LiFePO4

PHYSICAL

Lamp Base	Integrated
Finish	Gloss White
ANSI Base	Integrated
Lamp Type	Integrated LED
Fixture Shape	Rectangle
Mounting Procedure	Universal

ADDITIONAL INFO

Warranty	2-Years

PACKAGING

UPC	045923415692
Case Cube	1.0853
Case Height	11.02
Case Length	14.17
Case Quantity	4
Case UPC	10045923415699
Case Weight	26.9
Case Width	12.01
EA Cube	0.2202
EA Height	2.83
EA Length	13.39
EA Quantity	1
EA Weight	6.15
EA Width	10.04
Pack Type	Kraft Box
Web Height	9.13
Web Length	2.38
Web Width	12.13

COMPLIANCE

CA Prop 65	Lead
Dark Sky Rated	No
FCC Compliant	Yes
IP Rating	IP40
Location Rating	Damp
NSF Approved	No
ROHS Compliant	Yes
Safety Listing	cULus - Listed
California Ban	Non-Compliant
Energy Star Certified	No
Title 20	No
T24/JA8 Compliant	No
US State Ban	CA

© Satco Products, Inc.
All rights reserved 2026