SATCO | NUVO



Project / Job Name:

Location:

Fixture Type:

Notes:

S21349R1 - 5.5 Watt T10 LED; Frost Finish; Medium base; 90 CRI; 4000K; 120 Volt

WET LOCATION | 90+ CRI | DIMMABLE | ENCLOSED FIXTURE | c UL us LISTED | FC | RoHS COMPLIANT | 15,000 HOURS | 120 VOLT | TITLE 20

GENERAL

Company	SATCO
EA Height	5.39
EA Width	1.54
EA Length	1.54
Lamp Filament	LED Filament
Material	Glass / Nickel Plated Aluminum
Fixture Type	Tubular
Status	Active
Style	Traditional
Surge Protection	Built-in surge protection - 2.5KV
CCT Selectable	No
Wattage Selectable	No
Finish Family	White
Amps	0.062A
IOT Enabled	No
Operating Position	Universal
Power Factor	0.75
SDS Class	LED_Lamp
Indoor Outdoor	Indoor and Outdoor
Product Technology	LED
Incandescent Equivalent	40W
Serviceable Battery	No
Battery Indicator	No
Digital Display	No

ELECTRICAL

CCT (Kelvin Temp)	4000K
Dimmable	Yes-Dimmable
Hours Rated	15000
Beam Angle (degree)	320
Color Temp	Cool White
CRI	90+
Dimming Type	120V only, Phase Cut (TRIAC)
Operating Frequency	60Hz
Operating Temp	-4F to +113F (-20C to +45C)
Lumens	450L
Volts	120v
Watts	5.5W

PHYSICAL

Lamp Base	Medium
Finish	Frost
Housing Color	None
ANSI Base	E26
Lamp Type	T10
MOD Lamps	1.25
MOL	5.0

ADDITIONAL INFO

Warranty	2-Years
Installation Notes	Not for use in vapor tight fixtures.
Rated For Enclosed Fixture	Yes

PACKAGING

UPC	045923413360
Case Cube	0.2975
Case Height	5.59
Case Length	12.36
Case Quantity	24
Case UPC	10045923413367
Case Weight	3.1
Case Width	7.44
EA Cube	0.0074
EA Height	5.39
EA Length	1.54
EA Quantity	1
EA Weight	0.09
EA Width	1.54
Inner Cube	0.0585
Inner Height	5.16
Inner Length	5.71
Inner Quantity	6
Inner UPC	20045923413364
Inner Weight	0.65
Inner Width	3.43
Pack Type	Box
Web Length	5.0
Web Width	1.25

COMPLIANCE

FCC Compliant	Yes
Location Rating	Wet
NSF Approved	No
ROHS Compliant	Yes
Safety Listing	cULus - Certified, cULus - Listed
California Ban	Lawful for sale
Title 20	Yes
T24/JA8 Compliant	No

© Satco Products, Inc.
All rights reserved 2026