



Technical Data

Color	Bronze
Sizes Available	OS
Packaging	Bagged Each
Packed	144 Pair/Case
Case Dimensions (in)	23.62 x 14.76 x 16.73
Case Weight (lbs)	16.09
Country of Origin	Taiwan
Lens	Tinted
Frame Style	Semi-Rimless
Lens Color	Gray
Frame Fit	Universal
Lens Coating	Anti-Scratch, Anti-Fog
Bridge	Rubber
Temple	Bayonet
Base Curve	9.5
Certifications	ANSI Z87.1, TAA Compliant



Bouton® Optical Commander™

Semi-Rimless Safety Glasses with Gloss Bronze Frame, Brown Lens and Anti-Scratch / Anti-Fog Coating

- Lightweight, semi-rimless design offers extensive eye coverage and all day comfort
- Bayonet style temples with non-slip rubber pads provide a secure fit
- Adjustable rubber nose pads offer a custom, comfortable fit
- 9.5 Base curve lens
- Meets ANSI Z87.1+
- ⚠ **WARNING:** Reproductive Harm - www.P65Warnings.ca.gov

Applications

- Outdoor Work
- Construction Applications
- Public Works

SKU Information

SKU	FRAME COLOR	LENS	LENS COLOR	LENS	UPC	UPC (INNER)	UPC (CASE)
				COATING			
250-33-0010	Black	Clear	Clear	AS/AR	616314130342	01616314130341	02616314130340
250-33-0020	Black	Clear	Clear	AS/AF	616314130328	01616314130327	02616314130326
250-33-0021	Black	Tinted	Gray	AS/AF	616314130335	01616314130334	02616314130333
250-33-0041	Black	Polarized	Gray	AS	616314130366	01616314130365	02616314130364
250-33-0226	Black	Indoor Outdoor Blue	Clear	AS/AF	616314130359	01616314130358	02616314130357
250-33-1010	Bronze	Clear	Clear	AS/AR	616314130397	01616314130396	02616314130395
250-33-1020	Bronze	Clear	Clear	AS/AF	616314130373	01616314130372	02616314130371
250-33-1024	Bronze	Tinted	Gray	AS/AF	616314130380	01616314130389	02616314130388
250-33-1226	Bronze	Indoor Outdoor Blue	Clear	AS/AF	616314130403	01616314130402	02616314130401

KEY: AF = Anti-Fog / AR = Anti-Reflective / AS = Anti-Scratch / FL360 = Fogless 3Sixty / U = Uncoated