



JSP® Evolution® Deluxe 6151 Standard Brim Mining Hard Hat with HDPE Shell, 6-Point Polyester Suspension, Wheel Ratchet Adjustment and CR2 Reflective Kit

- Mining lamp bracket is non-corrosive and will receive 99% of the "World's Mining Lamps"
- Cable loop located on the rear of the hard hat keeps the cable in place
- CR2 high intensity reflective material offers 360° reflective coverage and significantly more reflectivity than standard reflective clothing material
- High-Density Polyethylene (HDPE) shell designed with five raised channels running across the top for strength, and an extended back area for extra protection
- 6-Point polyester textile suspension system offers unrivaled comfort without compromising performance
- Unique "3D Adjustment" provides a precise fit using harness depth settings...unlike any other hard hat on the US market today
- ⚠️ **WARNING:** Reproductive Harm - www.P65Warnings.ca.gov

Applications

- Construction Applications
- Road Work
- Excavation
- Industrial Applications



P65

Technical Data

Color	Blue, Neon Orange, White, Yellow, Red, Green, Neon Yellow
Sizes Available	OS
Packaging	Bagged Each
Packed	10/Case
Case Dimensions (in)	23.03 x 9.45 x 18.01
Case Weight (lbs)	8.82
Country of Origin	United Kingdom
Shell Material	HDPE
Shell	Non-Vented
Brim Style	Cap Style
Brim Length	Standard
Size Adjustment	Wheel Ratchet
Suspension	6 Point Polyester
Sweatband	Chamlon
Size Range	53cm-63cm
Certifications	ANSI/ISEA Z89.1, TAA Compliant
Product Circularity	Recycled via Terracycle

Performance Data

ANSI Type	Type I
Electrical Class	Class C

Care Instructions

The unit may be cleaned with soap and warm water and dried with a soft cloth. The helmet should not be cleaned with chemical or abrasive cleaners. The helmet should be stored out of direct sunlight, away from chemicals and not exposed to extremes of temperature.

SKU Information

SKU	COLOR	SIZE	UPC	UPC (INNER)	UPC (CASE)
280-EV6151MCR2-50	Blue	OS	616314167997	01616314167996	02616314167995
280-EV6151MCR2-30	Green	OS	616314185267	01616314185266	02616314185265
280-EV6151MCR2-OR	Neon Orange	OS	616314187216	01616314187215	02616314187214
280-EV6151MCR2-LY	Neon Yellow	OS	616314183584	01616314183583	02616314183582
280-EV6151MCR2-60	Red	OS	616314204159	01616314204158	02616314204157
280-EV6151MCR2-10	White	OS	616314153563	01616314153562	02616314153561
280-EV6151MCR2-20	Yellow	OS	616314167980	01616314167989	02616314167988